



Incremental encoder with solid shaft

RU-0250-I05/K

Article no longer available - archive entry



- 1 reference mark
2 M4 Depth 5 mm



CE

Product characteristics

Resolution	250 resolution
------------	----------------

Shaft design	solid shaft
--------------	-------------

Shaft diameter [mm]	6
---------------------	---

Electrical data

Operating voltage tolerance [%]	10
---------------------------------	----

Operating voltage [V]	5 DC
-----------------------	------

Current consumption [mA]	150
--------------------------	-----

Outputs

Electrical design	TTL
-------------------	-----

Max. current load per output [mA]	20
-----------------------------------	----

Switching frequency [kHz]	300
---------------------------	-----

Phase difference A and B [°]	90
------------------------------	----

Measuring/setting range

Resolution	250 resolution
------------	----------------

Operating conditions

Ambient temperature [°C]	-20...100
--------------------------	-----------

Storage temperature [°C]	-30...100
--------------------------	-----------

Max. relative air humidity [%]	98
--------------------------------	----


Protection	IP 64
------------	-------

RU1169



Incremental encoder with solid shaft

RU-0250-I05/K


Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		15 g (55...2000 Hz)
Mechanical data		
Dimensions	[mm]	Ø 58 / L = 56
Materials		aluminium
Max. revolution, mechanical [U/min]		12000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Fixing flange		synchro-flange
Electrical connection		
brown		A
green		A inverted
grey		B
pink		B inverted
red		0 index
black		0 index inverted
blue		L+ sensor
white		0V sensor
brown/green		L+ (Up)
white/green		0V (Un)
lilac		failure inverted
screen		housing
Connector: 1 x M23 (ifm 1001.4), radial		
		

Incremental encoder with solid shaft

RU-0250-I05/K

Diagrams and graphs

Pulse diagram



Output A

Output B

0 index

Article no longer available - archive entry
