


# RV1058



## Incremental encoder with solid shaft

RV-1800-I05/K

Article no longer available - archive entry



- 1 reference mark
- 2 M3 Depth 5 mm



### Product characteristics

Resolution	1800 resolution
Shaft design	solid shaft
Shaft diameter [mm]	10

### Electrical data

Operating voltage tolerance [%]	10
Operating voltage [V]	5 DC
Current consumption [mA]	150

### Outputs

Electrical design	TTL
Max. current load per output [mA]	20
Switching frequency [kHz]	300
Phase difference A and B [°]	90

### Measuring/setting range

Resolution	1800 resolution
------------	-----------------

### Operating conditions

Ambient temperature [°C]	-30...100
Storage temperature [°C]	-30...100
Max. relative air humidity [%]	98
Protection	IP 64

# RV1058



## Incremental encoder with solid shaft

RV-1800-105/K

### Tests / approvals

Shock resistance	100 g (6 ms)
Vibration resistance	15 g (55...2000 Hz)

### Mechanical data

Dimensions [mm]	Ø 58 / L = 75.5
Materials	aluminium
Max. revolution, mechanical [U/min]	12000
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	10
Shaft material	steel (1.4104)
Max. shaft load axial (at the shaft end) [N]	10
Max. shaft load radial (at the shaft end) [N]	20

### Electrical connection

Connector: 1 x M23 (ifm 1001.4), radial



1	B inverted
2	L+ sensor
3	0 index
4	0 index inverted
5	A
6	A inverted
screen	housing
7	failure inverted
8	B
9	n.c.
10	0V (Un)
11	0V sensor
12	L+

### Diagrams and graphs

Pulse diagram	<p>direction of rotation clockwise (looking at the shaft)</p>
---------------	---