




Incremental encoder with solid shaft

RB-0250-I05/L2

Article no longer available - archive entry



- 1 reference mark
2 M3 Depth 5 mm

CE

Product characteristics

Resolution		250 resolution
Shaft design		solid shaft
Shaft diameter [mm]		6
Electrical data		
Operating voltage tolerance [%]		10
Operating voltage [V]		5 DC
Current consumption [mA]		150
Outputs		
Electrical design		TTL
Max. current load per output [mA]		20
Switching frequency [kHz]		300
Phase difference A and B [°]		90
Measuring/setting range		
Resolution		250 resolution
Operating conditions		
Ambient temperature [°C]		-20...100
Storage temperature [°C]		-30...100
Max. relative air humidity [%]		98
Protection		IP 64
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)
Mechanical data		
Dimensions [mm]		Ø 36.5 / L = 38
Materials		aluminium

Incremental encoder with solid shaft

RB-0250-I05/L2

Max. revolution, mechanical [U/min]	10000
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	6
Shaft material	steel (1.4104)
Max. shaft load axial (at the shaft end) [N]	5
Max. shaft load radial (at the shaft end) [N]	10


Electrical connection

Cable: 2 m, PUR; radial, can also be used axially

brown	A
green	A inverted
grey	B
pink	B inverted
red	0 index
black	0 index inverted
blue	L+ sensor
white	0V sensor
brown/green	L+ (Up)
white/green	0V (Un)
lilac	failure inverted
screen	housing

Diagrams and graphs

Pulse diagram



direction of rotation clockwise (looking at the shaft)