
TM4341

Temperature sensor with process connection

TM-150KFBN12- /US/







Product characteristics			
Measuring range		-40150 °C	-40302 °F
Process connection			threaded connection 1/2" NPT
Installation length EL	[mm]		150
Application			
Special feature			Gold-plated contacts
Measuring element		1 x	Pt 100; (to DIN EN 60751, class A)
Media			liquids and gases
Pressure rating	[bar]		160
Minimum installation depth	[mm]		15
Electrical data			
Protection class			III
Measuring/setting range			
Probe length L	[mm]		142
Measuring range		-40150 °C	-40302 °F
Accuracy / deviations			
Accuracy	[K]		± (0,15 K + 0,002 x t)
Response times			
Dynamic response T05 / T09	[s]		1 / 3; (to DIN EN 60751)
Operating conditions			
Ambient temperature	[°C]		-2580
Storage temperature	[°C]	-40100	
Protection			IP 68; IP 69K
Tests / approvals			
Shock resistance		DIN EN 60068-2-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	10 g (102000 Hz)
MTTF [years]		22831
Mechanical data			
Weight	[g]		192.5

TM4341

Temperature sensor with process connection

TM-150KFBN12-

/US/



Materials		stainless steel (316L/1.4404)
Materials (wetted parts)		stainless steel (316L/1.4404)
Process connection		threaded connection 1/2" NPT
Probe diameter	[mm]	6
Installation length EL	[mm]	150

Remarks		
Remarks	operating voltage "supply class 2" according to cULus	
	The values for accuracy apply to flowing water.	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

