


RU-0120-I24/L2





Inkremental enkodere med massiv akse

RU-0120-I24/L2

Kapslingsklasse	IP 64
-----------------	-------

Godkendelser / Tests

Chokbestandig	100 g (6 ms)
Vibrationsbestandig	10 g (55...2000 Hz)

Mekaniske data

Dimensioner [mm]	Ø 58 / L = 46
Materiale	aluminium
Max. omdrejning, mekanisk [U/min]	12000
Max. startmoment [Nm]	1
Reference temperatur moment [°C]	20
Aksel design	massiv akse
Akseldiameter [mm]	6
Aksel materiale	stål (1.4104)
Max. akselbelastning aksial (ved aksel ende) [N]	10
Max. akselbelastning radial (ved aksel ende) [N]	20
Fastgørelsesflange	synkroflange

Elektrisk tilslutning

Kabel: 2 m, PUR; aksial

brun	A
grøn	A inverteret
grå	B
rosa	B inverteret
rød	0-Index
sort	0-Index inverteret
blå	L+ Sensor
hvid	0V Sensor
brun/grøn	L+ (Up)
hvid/grøn	0V (Un)
violet	fejl inverteret
Skærm	Kapsling

diagrammer og grafer

Impulsdiagram	 retning på rotation med uret (ses på akselenden)
---------------	--