


Pakning

U-SEAL 50 ST



Applikation

Medietemperatur	[°C]	-30...100
Trykbestandig	[bar]	400

Omgivende forhold

Omgivelsestemperatur	[°C]	-30...100
----------------------	------	-----------

Mekaniske data

Vægt	[g]	96,5
Indvendig diameter	[mm]	12
Ydre diameter	[mm]	21
Materiale		NBR; Stål

Bemærkning

Emballage-enheder		50 stk.
-------------------	--	---------