


G1506S



Safe AS-Interface ClassicLine module

Evaluation unit, asi

Article no longer available - archive entry




Electrical data		
Operating voltage	[V]	26.5...31.6 DC; (limited voltage requirements to UL 508: electrically isolated operating voltage protected by an overcurrent device)
Current consumption	[mA]	< 250
Inputs		
Sensor supply of the inputs		AS-i
Voltage supply	[V]	19.2...30; (via flat cable)
Digital inputs protected against short circuits		yes
Outputs		
Electrical design		AS-i
Voltage range DC	[V]	15...30; (to EN 50106 (PELV) via FC-E coupling module; via flat cable; limited voltage requirements to UL 508: electrically isolated operating voltage protected by an overcurrent device)
Max. current load per output	[mA]	500; (PNP)
Short-circuit proof		yes
Electrically separated		yes
Operating conditions		
Ambient temperature	[°C]	-25...55
Protection		IP 67
Tests / approvals		
EMC		EN 50295

G1506S



Safe AS-Interface ClassicLine module

Evaluation unit,asi

AS-i classification	
AS-i version	2.1
AS-i addressing	IR addressing possible
AS-i profile	S-7.B.E
AS-i I/O configuration [hex]	7
AS-i ID code [hex]	B.E
AS-i certificate	61801
Mechanical data	
Type of mounting	AS-i interface to FC/FC-E lower parts
Materials	PBT; potting compound: Guronic C400-0
Displays / operating elements	
Display	2 x LED, red
	2 x LED, green
	2 x LED, yellow
Accessories	
Accessories (supplied)	Protective caps M12
Remarks	
Pack quantity	1 pcs.
Electrical connection	
Connector: M12	
	

Article no longer available - archive entry