

DI001A




Compact evaluation unit for speed monitoring

DIA2010-ZROA/5-300 I/MIN/3D

Article no longer available - archive entry

Alternative articles: DI103A

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Output function		normally open
Sensing range	[mm]	10
Dimensions	[mm]	M30 x 1.5 / L = 81

Application

Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking
-------------	---

Electrical data

Nominal voltage AC	[V]	20...250
Nominal voltage DC	[V]	20...250
Nominal frequency AC	[Hz]	45...65
Protection class		II
Reverse polarity protection		yes

Outputs

Total number of outputs		1
Output function		normally open
Max. voltage drop switching output DC	[V]	6.5
Minimum load current	[mA]	6
Max. leakage current	[mA]	1.5
Permanent current rating of switching output AC	[mA]	200
Permanent current rating of switching output DC	[mA]	100
Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Short-circuit proof		no
Overload protection		no



Compact evaluation unit for speed monitoring

DIA2010-ZROA/5-300 I/MIN/3D

Detection zone		
Sensing range	[mm]	10
Sensing range adjustable		no
Measuring/setting range		
Setting range	[Imp/min]	5...300
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	10
Response times		
Start-up delay	[s]	12; (typical)
Max. damping frequency	[Imp/min]	1500
Software / programming		
Adjustment of the switch point		multiturn potentiometer
Operating conditions		
Ambient temperature	[°C]	-20...60
Protection		IP 67
Tests / approvals		
ATEX marking		II 3D Ex tD A22 IP67 T80°C X Ta: -20°C...+60°C
EMC	EN 60947-5-2	
Mechanical data		
Weight	[g]	0.256
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 81
Thread designation		M30 x 1.5
Materials		brass special coating; PBT
Displays / operating elements		
Display	switching status	1 x LED, green
Remarks		
Remarks	Recommendation Check the safe functioning of the unit after a short circuit.	

DI001A




Compact evaluation unit for speed monitoring

DIA2010-ZROA/5-300 I/MIN/3D

Electrical connection

Cable: 2 m, PVC; 2 x 0.5 mm²

Connection



Note miniature fuse to IEC60127-2 sheet 1 ≤ 2 A (fast acting) Place the fuse outside the hazardous area.

Core colours :

BN = brown

BU = blue