


DTE604



Compact RFID device with fieldbus interface

DTRHF HLRWENUS03



Application			
Radio approval for	USA; Canada; EU/RED; Australia; China; South Korea; Japan; Taiwan; Singapore; India; Malaysia; Vietnam		
Note on radio approval	The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under “Downloads”.		
Electrical data			
Operating voltage	[V]	19.2...28.8 DC	
Current consumption	[mA]	500	
Protection class		III	
Operating frequency	[MHz]	13,56	
RFID standard		ISO 15693	
Outputs			
Max. current load per output	[mA]	100; (max.)	
Detection zone			
Distance write/read head front	[mm]	600	
Distance write/read head side	[mm]	850	
Note on distance write/read head		100%	transmission power
Distance to the ID tag	[mm]	50 mm tag	≤ 150
		ISO card	≤ 180
Interfaces			
Communication interface	Ethernet		
Ethernet - TCP/IP			
Protocol	TCP/IP		
Factory settings	IP address: 192.168.0.79		
	subnet mask: 255.255.255.0		
	gateway IP address: 192.168.0.100		

DTE604



Compact RFID device with fieldbus interface

DTRHF HLRWENUS03

Usage type	parameter setting; data transmission
------------	--------------------------------------

Operating conditions

Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

Shock resistance	IEC 60028-2-27	40 g (6 ms) / bump
		50 g (11 ms) / single shock
Vibration resistance	EN 60068-2-6	2 g (10...150 Hz)
MTTF	[years]	130

Mechanical data

Weight	[g]	641.5
Dimensions	[mm]	113 x 118.5 x 50
Materials		PBT / PC; stainless steel; aluminium

Displays / operating elements

Display	power supply	1 x LED, green
	LED bar display	4 x LED, yellow signal strength ID tag
	status	2 x LED, green/red fieldbus interface
	status	2 x LED, green/yellow Ethernet

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - Ethernet

Connector: 2 x M12; coding: D




ETH1 / ETH2

1	TD+
2	RD+
3	TD-
4	RD-

Electrical connection - power supply

Connector: 1 x M12; coding: A



DTE604



Compact RFID device with fieldbus interface

DTRHF HLRWENUS03

PWR	
1	L+
2	digital input/output 2
3	L-
4	digital input/output 1
5	not used