




Inductive sensor

IOW2010-ARKG/0,15M/US/UP RT



1 snap-fit mounting



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	10
Housing	rectangular
Dimensions [mm]	26 x 26 x 26

Electrical data

Operating voltage [V]	10...36 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	2
Max. leakage current [mA]	0.6
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	250
Short-circuit protection	yes
Type of short-circuit protection	pulsed



Inductive sensor

IOW2010-ARKG/0,15M/US/UP RT

Overload protection	yes	
Detection zone		
Sensing range	[mm]	10
Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	2577
Mechanical data		
Weight	[g]	61.12
Housing	rectangular	
Mounting	flush mountable	
Dimensions	[mm]	26 x 26 x 26
Materials	PA	
Displays / operating elements		
Display	switching status	1 x LED, red
Accessories		
Items supplied	head cap screw: 1 x M4 x 12	
Remarks		
Pack quantity	1 pcs.	
Electrical connection - plug		
Cable: 0.15 m, PUR; 3 x 0.14 mm²		
Connector: 1 x M12; coding: A		
		

IO5018



Inductive sensor

IOW2010-ARKG/0,15M/US/UP RT

Connection

