




Inductive sensor

ILA3002-BPKG/MITTIG/0,31M/ASRT



- 1 Sensing face
2 countersink M2.5



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	2
Housing	rectangular
Dimensions [mm]	40 x 8 x 8

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	2
Real sensing range S_r [mm]	$2 \pm 10\%$
Operating distance [mm]	0...1.6



Inductive sensor

ILA3002-BPKG/MITTIG/0,31M/ASRT

Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	1...15	
Switch point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature		[°C]	-25...70
Protection			IP 65
Tests / approvals			
EMC		EN 60947-5-2	
MTTF		[years]	3449
UL approval		Ta	-25...70 °C
		Enclosure type	Type 1
		power supply	Limited Voltage/Current
		File number UL	E174191
Mechanical data			
Weight		[g]	23.4
Housing		rectangular	
Mounting		flush mountable	
Dimensions		[mm]	40 x 8 x 8
Materials		brass white bronze coated; sensing face: LCP	
Displays / operating elements			
Display		switching status	1 x LED, red
Accessories			
Items supplied		countersunk screws: 2 x M2,5 x 12	
Remarks			
Remarks		limited voltage requirements to UL 508: electrically isolated operating voltage protected by an overcurrent device	
Pack quantity		1 pcs.	
Electrical connection - plug			
Cable: 0.31 m, PUR / PVC			
Connector: 1 x M8; coding: A; Locking: knurled nut, rotatable			
			



IL5025



Inductive sensor

ILA3002-BPKG/MITTIG/0,31M/ASRT

Connection

