




Inductive analogue sensor with IO-Link

IMC4035A2PKG/F/IO/US



- 1 LED yellow
- 2 LED green



Product characteristics		
Electrical design		PNP/NPN; (parameterisable)
Output function		normally open / normally closed; (parameterisable)
Communication interface		IO-Link
Housing		rectangular
Dimensions	[mm]	40 x 40 x 54
Electrical data		
Operating voltage	[V]	15...30 DC
Current consumption	[mA]	< 33
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN; (parameterisable)
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	100



Inductive analogue sensor with IO-Link

IMC4035A2PKG/F/IO/US

Analogue voltage output	[V]	0...10; (linear; gradient: 0,3125 V/mm; for frontal approach and for target made of mild steel: 105 x 105 x 1 mm)	
Min. load resistance	[Ω]	2000	
Short-circuit protection		yes	
Overload protection		yes	
Detection zone			
Measuring range	[mm]	3...35	
Switch point IO-Link	[mm]	6.13...32.69	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.8 / brass: 0.5 / aluminium: 0.5 / copper: 0.4	
Hysteresis	[% of Sr]	3...15	
Note on hysteresis		parameterisable	
Linearity error of analogue output	[%]	± 2; (of the final value of the measuring range)	
Repeatability analogue output	[%]	± 2; (of the final value of the measuring range)	
Temperature coefficient		±0,15	
	[%/K vom MEW]		
Temperature drift		± 5 %; (of the final value of the measuring range)	
Response times			
Response time	[ms]	< 20	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
Profiles		Smart Sensor: Identification and diagnosis; Multi-channel, two setpoint switching sensor, type 0 Generic Profiled Sensor; Teach Channel	
SIO mode		yes	
Required master port type		A	
Min. process cycle time	[ms]	3.2	
IO-Link process data (cyclical)		function	bit length
		process value	16
		device status	4
		binary switching information	2
IO-Link functions (acyclical)		switching cycles counter; switch-on cycle counter; operating hours counter; internal temperature; application specific tag	
Supported DeviceIDs		Type of operation	DeviceID
		default	1206
Note		For further information please see the IODD PDF file under "Downloads"	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 67	



Inductive analogue sensor with IO-Link

IMC4035A2PKG/F/IO/US

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF	[years]	231
Embedded software included		yes
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current
	UL Approval no.	A026
	File number UL	E174191

Mechanical data		
Weight	[g]	158.5
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 40 x 54
Materials		PA; stainless steel (316L/1.4404)

Displays / operating elements		
Display	target in measuring range	1 x LED, yellow lights
	target outside measuring range	1 x LED, yellow flashing
	operation	LED, green

Remarks		
Remarks		Installation only with stainless steel plate 16x40x3 and 2 cylinder screws ISO 4762-12.9
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A



IM5175



Inductive analogue sensor with IO-Link

IMC4035A2PKG/F/IO/US

Connection



1	L +
2	OUT
3	L -
4	OUT / IO-Link