




Inductive sensor

ITB3001-BPOG/AS-500-TPS

Article no longer available - archive entry

Alternative articles: IT5021

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1
Housing	cylindrical
Dimensions [mm]	Ø 6.5 / L = 49

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	10; (24 V)
Reverse polarity protection	no

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	900
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	1
Real sensing range Sr [mm]	1 ± 10 %
Operating distance [mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

**Inductive sensor**

ITB3001-BPOG/AS-500-TPS

Mechanical data

Housing	cylindrical
Mounting	flush mountable
Dimensions [mm]	Ø 6.5 / L = 49
Materials	brass nickel-plated; PBT

Displays / operating elements

Display	switching status	1 x LED, red
---------	------------------	--------------

Accessories


Items supplied	Mounting clamps: 1
----------------	--------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A

**Connection**