




T-slot cylinder sensor

MKN3000-BPKG/0,3m AS-510-TPS

Article no longer available - archive entry

Alternative articles: MK5101

When selecting an alternative article and accessories please note that technical data may differ!



1 Sensing face



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	6.7 x 30 x 6

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Reverse polarity protection	yes
Max. power-on delay time [ms]	2

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Response sensitivity [mT]	3
Travel speed [m/s]	< 5

Accuracy / deviations

Hysteresis [mm]	1.5
Repeatability [mm]	0.2

Operating conditions

Ambient temperature [°C]	-25...75
--------------------------	----------

MK5019



T-slot cylinder sensor

MKN3000-BPKG/0,3m AS-510-TPS

Protection	IP 67
------------	-------

Tests / approvals

EMC	EN 60947-5-2
Shock/vibration resistance	30 g (11 ms) / 10-55 Hz (1 mm)

Mechanical data

Sensing face	front
Cylinder type	T-slot cylinders
Dimensions [mm]	6.7 x 30 x 6
Materials	plastics

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Cable: 0.3 m, PUR / PVC

Connector: 1 x M8; coding: A



Connection

