


KQ5005



Capacitive sensor

KQ-3073NAPKG



- 1 LED
2 Sensing face



Product characteristics	
Electrical design	PNP
Output function	normally closed
Sensing range [mm]	7.3; (fixed: 7,3)
Housing	rectangular
Dimensions [mm]	57 x 36 x 10
Application	
Application	level detection of demineralised water
Electrical data	
Operating voltage [V]	10...30 DC
Current consumption [mA]	< 17
Protection class	III
Reverse polarity protection	yes
Outputs	
Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	10
Short-circuit proof	yes
Overload protection	yes
Detection zone	
Sensing range [mm]	7.3; (fixed: 7,3)
Accuracy / deviations	
Correction factor	glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-20...20

KQ5005



Capacitive sensor

KQ-3073NAPKG

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65; IP 67; IP 69K

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	771
UL approval	Ta	-25...80 °C
	Enclosure type	Type 1
	power supply	Class 2

Mechanical data

Weight	[g]	67.7
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	57 x 36 x 10
Materials		PBT; TPE-U; stainless steel

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	mounting adapter: 1
----------------	---------------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PUR; 3 x 0.14 mm²

Connection



BN	Core colours :
BK	brown
BU	black
	blue