


O3M251



3D sensor for mobile applications

O3MXOOKG/CAN/E3/GM/A1/70



Product characteristics

Type of light		infrared light
Image resolution	[px]	640 x 480
Image resolution 3D	[px]	64 x 16
Angle of aperture	[°]	90 x 67
Angle of aperture 3D	[°]	70 x 23
Image repetition frequency	[Hz]	25
Image repetition frequency 3D	[Hz]	25 / 33 / 50

Application

Application	output of 3D image data; output of 2D image data
-------------	--

Electrical data

Operating voltage	[V]	9...32 DC
Current consumption	[mA]	< 600
Power consumption	[W]	4.6



3D sensor for mobile applications

O3MXOOKG/CAN/E3/GM/A1/70

Protection class	III	
Type of light	infrared light	
Image sensor	PMD 3D ToF-Chip / 2D Chip	
Outputs		
Video output	PAL (720x576)	
Detection zone		
Image resolution	[px]	640 x 480
Image resolution 3D	[px]	64 x 16
Angle of aperture	[°]	90 x 67
Angle of aperture 3D	[°]	70 x 23
Image repetition frequency	[Hz]	25
Image repetition frequency 3D	[Hz]	25 / 33 / 50
Software / programming		
Parameter setting options	via PC with ifm Vision Assistant	
Interfaces		
Communication interface	CAN; Ethernet	
Number of CAN interfaces	1	
Number of Ethernet interfaces	1	
Number of video interfaces (CVBS)	1	
Note on interfaces	Output of preprocessed data via CAN interface	
CAN		
Transmission rate	250 (125...1000) kBaud	
Protocol	CANopen; UDS	
Factory settings	J1939 interface: Default	
	device address (ECU): 239	
	UDS interface: 500 (125...1000) kBaud	
Usage type	parameter setting; data transmission	
Ethernet		
Protocol	UDP/IP	
Factory settings	IP address: 192.168.1.1	
	subnet mask: 255.255.255.0	
	target IP address: 255.255.255.255	
	target port: 42000	
Usage type	data transmission	
Operating conditions		
Ambient temperature	[°C]	-40...85
Note on ambient temperature	with high image repetition frequency of 25 Hz	
Storage temperature	[°C]	-40...105
Max. relative air humidity	[%]	90; (non condensing)
Max. height above sea level	[m]	4000
Protection	IP 67; IP 69K; (with mounted connectors or protective caps)	



3D sensor for mobile applications

O3MXOOKG/CAN/E3/GM/A1/70

Max. immunity to extraneous light	[klx]	120
-----------------------------------	-------	-----

Tests / approvals

EMC	DIN EN 61000-6-4	industrial environments
	DIN EN 61000-6-2	industrial environments
Shock resistance	DIN EN 60068-2-27	30 g / 6 ms bump
Vibration resistance	DIN EN 60068-2-6	10 g / 10...500 Hz swept sine
	DIN EN 60068-2-64	10...1000 Hz noise
Electrical protection	DIN EN 61010-2-201	electric shock / electrical supply only via PELV circuits
MTTF	[years]	58

Mechanical data

Weight	[g]	1155
Dimensions	[mm]	143.8 x 85 x 70.1
Materials	housing: diecast aluminium; disc: gorilla glass	

Accessories


Items supplied	Protective covers
----------------	-------------------

Remarks

Remarks	The illumination unit is required for the operation of the sensor.
	Only use original ifm cables to connect sensor and illumination unit.
	The function-specific performance values can be found in the applicable documentation.
Pack quantity	1 pcs.

Electrical connection - CAN

Connector: 1 x M12; coding: A



1	Screen
2	9...32 V
3	GND
4	CAN-H
5	CAN-L

O3M251



3D sensor for mobile applications

O3MXOOKG/CAN/E3/GM/A1/70

Electrical connection - Ethernet


Connector: 1 x M12; coding: D



1	TD +
2	RD +
3	TD -
4	RD -

Electrical connection - video

Connector: 1 x M12; coding: A



2	not used
3	GND
4	FBAS
5	not used

Other data

field of view size with lens distortion correction

measuring range / distance [m]	Length [m]	Width [m]
5	7	2
10	14	4.1
15	21	6.5
30	42	12.2



3D sensor for mobile applications

O3MXOOKG/CAN/E3/GM/A1/70

measuring range for object recognition

object type / object size	application condition	Measuring range [m]
vehicle	sunny (~120 klx)	0.25...30
	cloudy (~20 klx)	0.25...40
	darkness	0.25...50
person	sunny (~120 klx)	0.25...12
	cloudy (~20 klx)	0.25...16
	darkness	0.25...20
retroreflector	sunny (~120 klx)	1...40
	cloudy (~20 klx)	1...60
	darkness	1...80
software variant:		OD object recognition

measuring range for ROI

application condition	Measuring range [m]
	typical value
sunny (~120 klx)	0.25...12
cloudy (~20 klx)	0.25...15
darkness	0.25...30
software variant :	DI / BF distance image basic functions

measuring accuracy

application condition	measuring accuracy [cm]
	typical value
sunny (~120 klx)	± 15
cloudy (~20 klx)	± 10
darkness	± 5
software variant :	DI / BF distance image basic functions