



Through-beam sensor transmitter

OGS-OOKG/US-100 MIT 90GRAD WKL

Article no longer available - archive entry

Alternative articles: OG5129

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Special feature	Gold-plated contacts
Function principle	Through-beam sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 17
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Transmitter / receiver	transmitter
Range [m]	< 12
Range adjustable	no



Through-beam sensor transmitter

OGS-OOKG/US-100 MIT 90GRAD WKL

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Housing		threaded type
Dimensions	[mm]	M18 x 1
Thread designation		M18 x 1
Materials		PBT
Lens material		PMMA
Displays / operating elements		
Display	operation	1 x LED, green
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		



Connection

