




Pressure sensor with display

PN-600-SE MFRKG/US/ I



- 1 LEDs Display unit switching status
- 2 analogue display, 4-digit alphanumeric display
- 3 programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	0...600 bar	0...8700 psi
Measuring range [MPa]	0...60	
Process connection	homogeniser connection	

Application

Special feature	Gold-plated contacts	
Measuring element	diaphragm seal	
Application	flush mountable for the food and beverage industry	
Media	liquids and gases	
Medium temperature [°C]	5...90; (for further details see section Diagrams and graphs)	
Min. bursting pressure	1200 bar	17400 psi
Min. bursting pressure [MPa]	120	
Pressure rating	800 bar	11580 psi
Pressure rating [MPa]	80	
Vacuum resistance [mbar]	-1000	



Pressure sensor with display

PN-600-SE MFRKG/US/ /

Type of pressure	relative pressure	
Electrical data		
Operating voltage	[V]	18...30 DC; (to SELV/PELV)
Current consumption	[mA]	< 35
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.3
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Outputs		
Total number of outputs	2	
Output signal	switching signal; analogue signal; IO-Link; (configurable)	
Electrical design	PNP/NPN	
Number of digital outputs	2	
Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	< 500
Number of analogue outputs	1	
Analogue current output	[mA]	4...20; (scalable 1:5)
Max. load	[Ω]	500
Analogue voltage output	[V]	0...10; (scalable 1:5)
Min. load resistance	[Ω]	2000
Short-circuit protection	yes	
Type of short-circuit protection	pulsed	
Overload protection	yes	
Measuring/setting range		
Measuring range	0...600 bar	0...8700 psi
Measuring range	[MPa]	0...60
Set point SP	4...600 bar	60...8700 psi
Set point SP	[MPa]	0.4...60
Reset point rP	1...597 bar	20...8660 psi
Reset point rP	[MPa]	0.1...59.7
Analogue start point	0...480 bar	0...6960 psi
Analogue start point	[MPa]	0...48
Analogue end point	120...600 bar	1740...8700 psi
Analogue end point	[MPa]	12...60
In steps of	1 bar	20 psi
In steps of	[MPa]	0.1



Pressure sensor with display

PN-600-SE MFRKG/US/ /

Accuracy / deviations		
Switch point accuracy [% of the span]	< ± 0,4; (Turn down 1:1)	
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation [% of the span]	< ± 1; (linearity, incl. hysteresis and repeatability; limit value setting to DIN EN IEC 62828-1)	
Hysteresis deviation [% of the span]	< ± 0,1; (Turn down 1:1)	
Long-term stability [% of the span]	< ± 0,05; (Turn down 1:1; per 6 months)	
Temperature coefficient zero point [% of the span / 10 K]	0,2; (5...80 °C)	
Temperature coefficient span [% of the span / 10 K]	0,2; (5...80 °C)	
Response times		
Response time [ms]	< 1.5	
Delay time programmable dS, dr [s]	0...50	
Damping process value dAP [s]	0...4	
Damping for the analogue output dAA [s]	0...4	
Max. response time analogue output [ms]	3	
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switch-on/ switch-off delay; Damping; Display unit; current/voltage output	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port type	A	
Process data analogue	1	
Process data binary	2	
Min. process cycle time [ms]	2.3	
Supported DeviceIDs	Type of operation	DeviceID
	default	458
Operating conditions		
Ambient temperature [°C]	5...80	
Storage temperature [°C]	-40...100	
Protection	IP 67	

PY9060



Pressure sensor with display

PN-600-SE MFRKG/US/ I

Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	10 g (10...2000 Hz)
MTTF	[years]	143
Mechanical data		
Weight	[g]	675
Materials	stainless steel (630/1.4542/17-4 PH); stainless steel (316L/1.4404); stainless steel (316L/1.4435); PBT+PC-GF30; PBT-GF20; PC	
Materials (wetted parts)	stainless steel (316L/1.4435)	
Min. pressure cycles	60 million; (at 1.2 times nominal pressure)	
Process connection	homogeniser connection	
Displays / operating elements		
Display	Display unit	3 x LED, green (bar, psi, MPa)
	switching status	2 x LED, yellow
	measured values	alphanumeric display, red/green 4-digit
Remarks		
Pack quantity	1 pcs.	

PY9060




Pressure sensor with display

PN-600-SE MFRKG/US/ /

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated




OUT1 switching output or IO-Link
OUT2 switching output or analogue output
colours to DIN EN 60947-5-2

Core colours :

BK = black
BN = brown
BU = blue
WH = white

Diagrams and graphs



X Ambient temperature

Y Medium temperature