


SM0504



Magnetic-inductive flow meter

SMR11GGX50KG/US100



Product characteristics		
Number of inputs and outputs	Number of analogue outputs: 2	
Measuring range	6...1800 gph	0.1...30 gpm
Process connection	threaded connection G 1 DN25 flat seal	
Application		
Special feature	Gold-plated contacts	
Application	for industrial applications	
Installation	connection to pipe by means of an adapter	
Media	conductive liquids; water; hydrous media	
Note on media	conductivity: ≥ 20 μS/cm	
	viscosity: < 70 mm²/s (40 °C)	
Medium temperature	[°F]	14...158
Pressure rating	[bar]	16
Pressure rating	[psi]	232
Electrical data		
Operating voltage	[V]	18...30 DC; (to SELV/PELV)
Current consumption	[mA]	95; (24 V)
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	5
Inputs / outputs		
Number of inputs and outputs	Number of analogue outputs: 2	
Outputs		
Total number of outputs	2	
Output signal	analogue signal	



Magnetic-inductive flow meter

SMR11GGX50KG/US100

Number of analogue outputs		2
Analogue current output [mA]		4...20; (scalable)
Max. load [Ω]		500
Overload protection		yes
Measuring/setting range		
Measuring range		6...1800 gph0.1...30 gpm
Display range		-1902...1902 gph-31.7...31.7 gpm
Resolution		2 gph0.05 gpm
Analogue start point ASP		0...1268 gph0...21.15 gpm
Analogue end point AEP		318...1800 gph5.3...30 gpm
In steps of		2 gph0.05 gpm
Temperature monitoring		
Measuring range [°F]		-4...176
Resolution [°F]		0.5
Analogue start point [°F]		-4...140.5
Analogue end point [°F]		31.5...176
In steps of [°F]		0.5
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		± (0,8 % MW + 0,5 % MEW)
Repeatability		± 0,2% MEW
Temperature monitoring		
Accuracy [K]		± 4,5 (Q > 0,26 gpm)
Response times		
Flow monitoring		
Response time [s]		0.15; (dAP = 0)
Damping process value dAP [s]		0...5
Temperature monitoring		
Dynamic response T05 / T09 [s]		T09 = 20 (Q > 0,26 gpm)
Operating conditions		
Ambient temperature [°F]		14...140
Storage temperature [°F]		-13...176
Protection		IP 67
Tests / approvals		
EMC		DIN EN 60947-5-9500 V withstand voltage (V DC)
Shock resistance		DIN IEC 68-2-2720 g (11 ms)
Vibration resistance		DIN IEC 68-2-65 g (10...2000 Hz)
MTTF [years]		175
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight [g]		576
Materials		stainless steel (316L/1.4404); PBT-GF20; PC; EPDM/X
Materials (wetted parts)		stainless steel (316L/1.4404); Hastelloy; PEEK; FKM

SM0504



Magnetic-inductive flow meter

SMR11GGX50KG/US100

Process connection	threaded connection G 1 DN25 flat seal
--------------------	--

Displays / operating elements

Display	Display unit	6 x LED, green (l/min, m³/h, gpm, gph, °C, °F)
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit
Display unit	l/min; m³/h; gpm; gph; °C; °F	

Remarks


Remarks	MW = measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1:	analogue output Temperature monitoring
OUT2:	analogue output volumetric flow quantity monitoring

SM0504




Magnetic-inductive flow meter

SMR11GGX50KG/US100

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity