


SM8050



Magnetic-inductive flow meter

SMR11GGX10KG/US



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1
Measuring range [l/min]	0.2...100
Process connection	threaded connection G 1 DN25 flat seal

Application

Special feature	Gold-plated contacts
Application	for industrial applications
Installation	connection to pipe by means of an adapter
Media	conductive liquids; water; hydrous media
Note on media	conductivity: $\geq 20 \mu\text{S/cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)
Medium temperature [°C]	-10...70
Pressure rating [bar]	16
Pressure rating [MPa]	1.6
MAWP (for applications according to CRN) [bar]	11.2

Electrical data

Operating voltage [V]	18...30 DC; (to SELV/PELV)
Current consumption [mA]	95; (24 V)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	5

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
-------------------------	---

SM8050



Magnetic-inductive flow meter

SMR11GGX10KG/US

Output signal	analogue signal; IO-Link; (configurable)	
Permanent current rating of switching output DC [mA]	250	
Number of analogue outputs	1	
Analogue current output [mA]	4...20	
Max. load [Ω]	500	
Overload protection	yes	

Measuring/setting range

Measuring range [l/min]	0.2...100
-------------------------	-----------

Accuracy / deviations

Flow monitoring		
Accuracy (in the measuring range)	± (0,8 % MW + 0,5 % MEW)	
Repeatability	± 0,2% MEW	

Response times

Flow monitoring		
Response time [s]	0.15; (dAP = 0, T19)	

Interfaces

Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port type	A	
Process data analogue	2	
Min. process cycle time [ms]	3	
Supported DeviceIDs	Type of operation	DeviceID
	default	577

Operating conditions

Ambient temperature [°C]	-10...60
Storage temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	DIN EN 60947-5-9	
CPA approval	model number	002MI
	accuracy class	-
	maximum allowable error	± 1,5 % FS
	Q (min)	0,01 m³/h
	Q (t)	-
	Q (max)	6 m³/h
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)
MTTF [years]	167	
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

SM8050



Magnetic-inductive flow meter

SMR11GGX10KG/US

Mechanical data		
Weight	[g]	575
Materials	stainless steel (316L/1.4404); PBT-GF20; FKM; TPE	
Materials (wetted parts)	stainless steel (316L/1.4404); PEEK; FKM	
Process connection	threaded connection G 1 DN25 flat seal	


Remarks		
Remarks	MW = measured value	
	MEW = Final value of the measuring range	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated




Connection



OUT1: colours to DIN EN 60947-5-2
OUT2: IO-Link
Core colours :
BN = brown
WH = white
BK = black
BU = blue

SM8050




Magnetic-inductive flow meter

SMR11GGX10KG/US

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity