


Alternative articles: SI2100

When selecting an alternative article and accessories please note that technical data may differ!



Number of inputs and outputs	Number of digital outputs: 1
Process connection	Varivent DN25

Application	hygienic applications
Medium temperature [°C]	-25...95
Pressure rating [bar]	30

Operating voltage	[V]	20...36 DC
Current consumption	[mA]	< 45
Reverse polarity protection		yes
Power-on delay time	[s]	< 20

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

ST0516



Flow monitor

SCG15ABBFPKG/US-100-IPF

Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	400
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Accuracy / deviations		
Temperature gradient	[K/min]	15
Response times		
Response time	[s]	1...10
Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature	[°C]	-20...30
Protection		IP 67
Mechanical data		
Dimensions	[mm]	72 x 41 x 83
Materials		PBT-GF20
Materials (wetted parts)		stainless steel (316Ti/1.4571)
Process connection		Varivent DN25
Displays / operating elements		
Display	function	11 x LED
Remarks		
Pack quantity		1 pcs.

ST0516



Flow monitor

SCG15ABBFPKG/US-100-IPF

Electrical connection

Connector: 1 x M12; coding: A



Connection

