PI2664


Flush pressure sensor with display

PI-010-REA01-MFRKG/US/ /P

Article no longer available - archive entry

Alternative articles: PI2694 or PI1694

When selecting an alternative article and accessories please note that technical data may differ!



1 7-segment LED display
2 programming button
3 Tightening torque 20 Nm
4 diaphragm : PTFE

Product characteristics			
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	-0.5...10 bar	-7...145 psi	-50...1000 kPa
Process connection	threaded connection G 1 external thread		
Application			
Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	freely rotatable housing 350°		
Media	liquid and viscous media		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	150 bar	2175 psi	15000 kPa
Pressure rating	50 bar	725 psi	5000 kPa
Type of pressure	relative pressure		

PI2664

Flush pressure sensor with display

PI-010-REA01-MFRKG/US/ /P

No dead space		yes		
Electrical data				
Operating voltage	[V]	20...30 DC; ("supply class 2" to cULus)		
Current consumption	[mA]	< 60		
Min. insulation resistance	[MΩ]	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	0.2		
Integrated watchdog		yes		
Inputs / outputs				
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1		
Outputs				
Total number of outputs		2		
Output signal		switching signal; analogue signal; (configurable)		
Electrical design		PNP/NPN		
Number of digital outputs		2		
Output function		normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	250		
Switching frequency DC	[Hz]	< 170		
Number of analogue outputs		1		
Analogue current output	[mA]	4...20; (scalable 1:4)		
Max. load	[Ω]	(Ub - 10 V) / 20 mA		
Analogue voltage output	[V]	0...10; (scalable 1:4)		
Min. load resistance	[Ω]	2000		
Short-circuit protection		yes		
Type of short-circuit protection		pulsed		
Overload protection		yes		
Measuring/setting range				
Measuring range		-0.5...10 bar	-7...145 psi	-50...1000 kPa
Set point SP		-0.45...9.99 bar	-7...145 psi	-45...999 kPa
Reset point rP		-0.5...9.94 bar	-7...144 psi	-50...994 kPa
Analogue start point		-0.5...7.49 bar	-7...109 psi	-50...749 kPa
Analogue end point		2...9.99 bar	29...145 psi	200...999 kPa
In steps of		0.01 bar	1 psi	1 kPa
Accuracy / deviations				
Repeatability	[% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)		
Characteristics deviation	[% of the span]	< ± 0,6; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)		
Linearity deviation	[% of the span]	< ± 0,5; (Turn down 1:1)		
Hysteresis deviation		< ± 0,1; (Turn down 1:1)		

PI2664

Flush pressure sensor with display

PI-010-REA01-MFRKG/US/ /P

[% of the span]		
Long-term stability [% of the span]		< ± 0,1; (Turn down 1:1; per year)
Temperature coefficient zero point [% of the span / 10 K]		< ± 0,15; (0...80 °C)
Temperature coefficient span [% of the span / 10 K]		< ± 0,4; (0...80 °C)
Response times		
Response time [ms]		< 3
Damping process value dAP [s]		0...4
Damping for the analogue output dAA in steps [s]		0 - 0,1 - 0,5 - 2
Max. response time analogue output [ms]		3
Software / programming		
Parameter setting options		hysteresis / window; normally open / normally closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; zero point; span
Operating conditions		
Ambient temperature [°C]		-25...80
Storage temperature [°C]		-40...100
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Materials		stainless steel (1.4404 / 316L); PBT; PC; PA; EPDM/X; FKM
Materials (wetted parts)		stainless steel (1.4435 / 316L); PTFE on ceramic substrate; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection G 1 external thread
Displays / operating elements		
Display	switching status	2 x LED, red
	function display	7-segment LED display
	measured values	7-segment LED display
Display unit		bar; psi; kPa
Remarks		
Pack quantity		1 pcs.

PI2664

Flush pressure sensor with display


PI-010-REA01-MFRKG/US/ /P


Electrical connection


Connector: 1 x M12; coding: A; Contacts: gold-plated




Connection









OUT1	switching output
OUT2	switching output analogue output