


# RO6339



## Incremental encoder with hollow shaft

RO-2500-I24/N11

Article no longer available - archive entry



### Product characteristics

Resolution		2500 resolution
Shaft design		continuous hollow shaft
Shaft diameter	[mm]	10

### Application

Function principle		incremental
--------------------	--	-------------

### Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 150

### Outputs

Electrical design		HTL
Max. current load per output	[mA]	50
Switching frequency	[kHz]	300
Type of short-circuit protection		< 60 s
Phase difference A and B	[°]	90

### Measuring/setting range

Resolution		2500 resolution
------------	--	-----------------

### Operating conditions

Ambient temperature	[°C]	-30...85
Note on ambient temperature		for firmly laid cable: -30 °C
Max. relative air humidity	[%]	98
Protection		IP 64; (on the housing: IP 66; on the shaft: IP 64)

# RO6339



## Incremental encoder with hollow shaft

RO-2500-I24/N11

Tests / approvals	
Shock resistance	200 g
Vibration resistance	30 g
Mechanical data	
Weight [g]	454.6
Dimensions [mm]	Ø 58 / L = 54.4
Materials	aluminium
Max. revolution, mechanical [U/min]	12000; (when using both shaft clamping rings)
Max. starting torque [Nm]	2.5
Reference temperature [°C]	20
Shaft design	continuous hollow shaft
Shaft diameter [mm]	10
Shaft fit	H7
Shaft material	stainless steel
Installation depth of shaft [mm]	10
Max. axial shaft misalignment [mm]	1; (max. radial shaft alignment: ± 0,05 mm)

### Electrical connection

Cable: 1 m, PUR; radial, can also be used axially

brown	A
green	A inverted
grey	B
pink	B inverted
red	0 index
black	0 index inverted
blue	L+ sensor
white	0V sensor
brown/green	L+ (Up)
white/green	0V (Un)
screen	housing
lilac	failure inverted

### Diagrams and graphs

Pulse diagram	<p>direction of rotation clockwise (looking at the shaft)</p>
---------------	---