
SD8000

Compressed air meter

SDR11DGXFPKG/US-100

phase-out article
Discontinuation date: 12/31/2024

Alternative articles: SD8500
When selecting an alternative article and accessories please note that technical data may differ!



1 alphanumeric display 4-digit
2 programming buttons

Product characteristics			
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	13...3750 l/min	0.4...109.2 m/s	0.7...225 m³/h
Process connection	threaded connection R 1 DN25		
Application			
Application	for industrial applications		
Media	compressed air		
Note on media	air quality ISO 8573-1		
	class 141		
	class 344		
Medium temperature [°C]	0...60		
Pressure rating [bar]	16		
Pressure rating [MPa]	1.6		
Electrical data			
Operating voltage [V]	18...30 DC; (to SELV/PELV)		
Current consumption [mA]	< 110		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	1		

SD8000

Compressed air meter

SDR11DGXFPKG/US-100

Inputs / outputs				
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1		
Outputs				
Total number of outputs		2		
Output signal		switching signal; analogue signal; pulse signal; IO-Link; (configurable)		
Electrical design		PNP		
Number of digital outputs		2		
Output function		normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	250; (per output)		
Number of analogue outputs		1		
Analogue current output	[mA]	4...20; (scalable)		
Max. load	[Ω]	500		
Pulse output		consumed quantity meter		
Short-circuit protection		yes		
Type of short-circuit protection		pulsed		
Overload protection		yes		
Measuring/setting range				
Measuring range		13...3750 l/min	0.4...109.2 m/s	0.7...225 m³/h
Display range		0...4500 l/min	0...131 m/s	0...270 m³/h
Set point SP		30...3750 l/min	0.9...109.2 m/s	1.8...225 m³/h
Reset point rP		12...3732 l/min	0.4...108.7 m/s	0.7...223.9 m³/h
Analogue start point ASP		0...2813 l/min	0...81.9 m/s	0...168.8 m³/h
Analogue end point AEP		937...3750 l/min	27.3...109.2 m/s	56.2...225 m³/h
In steps of		1 l/min	0.1 m/s	0.1 m³/h
Volumetric flow quantity monitoring				
Pulse value		0.003...3000000 m³		
In steps of		0.001 m³		
Pulse length	[s]	0,02...2		
Temperature monitoring				
Measuring range	[°C]	0...60		
Display range	[°C]	-12...72		
Accuracy / deviations				
Flow monitoring				
Repeatability	[% of the measured value]	± 1,5		
Accuracy (in the measuring range)		± (3 % MW + 0,3 % MEW) / ± (6 % MW + 0,6 % MEW); (class 141 /; class 344; conditions: installation to DIN ISO 2533; installation in pipes: DN25)		
Temperature monitoring				
Accuracy	[K]	± 2; (medium flow in the limit area of the flow measurement range)		

SD8000

Compressed air meter

SDR11DGXFPKG/US-100

Response times			
Flow monitoring			
Response time	[s]	0.1; (dAP = 0)	
Damping process value dAP in steps	[s]	0 - 0,2 - 0,4 - 0,6 - 0,8 - 1	
Software / programming			
Parameter setting options		Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / normally closed; current/pulse output; display can be rotated and switched off; Display unit; totaliser	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9 CDV	
Profiles		no profile	
SIO mode		yes	
Required master port type		A	
Process data analogue		3	
Process data binary		2	
Min. process cycle time	[ms]	4.1	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	267
Operating conditions			
Ambient temperature	[°C]	0...60	
Storage temperature	[°C]	-20...85	
Max. relative air humidity	[%]	90	
Protection		IP 65	
Tests / approvals			
EMC		DIN EN 61000-6-2	
		DIN EN 61000-6-3	
CPA approval		model number	002TG
		accuracy class	-
		maximum allowable error	± 4 % FS
		Q (min)	0,7 m³/h
		Q (t)	-
		Q (max)	225 m³/h
Vibration resistance		DIN EN 68000-2-6	5 g (55...2000 Hz)
MTTF	[years]	227	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight	[g]	2029	
Materials		PBT-GF20; NBR; PC; stainless steel (1.4301 / 304); PTFE; brass coated; FKM; aluminium powder-coated	
Materials (wetted parts)		stainless steel (1.4301 / 304); FKM; ceramics glass passivated; PEEK GF30; polyester; aluminium	
Process connection		threaded connection R 1 DN25	

SD8000

Compressed air meter

SDR11DGXFPKG/US-100

Displays / operating elements		
Display	Display unit	5 x LED, green (Nl/min, Nm³/h, Nm/s, Nm³, °C)
	function display	1 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit


Remarks	
Remarks	MW = measured value
	MEW = Final value of the measuring range
	Measuring, display and setting ranges refer to the standard volume flow according to DIN ISO 2533.
	For information about installation and operation please see the operating instructions.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection



OUT1/IO-Link:	switching output volumetric flow quantity monitoring Pulse output quantity meter signal output Preset counter
OUT2/InD:	switching output volumetric flow quantity monitoring / Temperature monitoring analogue output volumetric flow quantity monitoring / Temperature monitoring input counter reset