




AS-Interface CANopen gateway with PLC

ControllerE M4 2Master CO

Article no longer available - archive entry



Application	
Application	decentralised controller; CANopen gateway
Electrical data	
Operating voltage [V]	24 DC
Current consumption [mA]	< 500
Max. current consumption from AS-i [mA]	10
Max. power consumption [VA]	10
Number of AS-i masters	2
Interfaces	
Communication interface	RS232; CAN
CAN	
Number of CAN interfaces	1
Protocol	CANopen
Usage type	data transmission



AS-Interface CANopen gateway with PLC

ControllerE M4 2Master CO

RS232		
Number of R232 interfaces		1
Transmission rate		9600...115200 Baud
Connector type		RJ11
Usage type		programming
Note on interfaces		electrically isolated
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Protection		IP 20
AS-i classification		
AS-i version		2.11; 3.0
AS-i master profile		M4
Mechanical data		
Weight	[g]	584.5
Housing		housing for DIN rail mounting
Materials		aluminium; steel sheet galvanised
Displays / operating elements		
Display	function	4 x LED, red
		3 x LED, green
		3 x LED, yellow
		full graphic LCD display
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Connection		

