

# AC1321




## AS-Interface CANopen gateway with PLC

ControllerE 1Mstr CO RS232

Article no longer available - archive entry

Alternative articles: AC1331

When selecting an alternative article and accessories please note that technical data may differ!



### Application

Application	decentralised controller; CANopen gateway
-------------	---

### Electrical data

Operating voltage	[V]	24 DC
Current consumption	[mA]	< 500
Max. current consumption from AS-i	[mA]	10
Max. power consumption	[VA]	10
Number of AS-i masters		1

### Interfaces

Communication interface	RS232; CAN
-------------------------	------------

# AC1321



## AS-Interface CANopen gateway with PLC

ControllerE 1Mstr CO RS232

CAN		
Number of CAN interfaces	1	
Protocol	CANopen	
Usage type	data transmission	
RS232		
Number of R232 interfaces	1	
Transmission rate	9600...115200 Baud	
Connector type	RJ11	
Usage type	programming	
Note on interfaces	electrically isolated	
Operating conditions		
Ambient temperature [°C]	0...60	
Storage temperature [°C]	-20...70	
Max. relative air humidity [%]	95	
Protection	IP 20	
AS-i classification		
AS-i version	2.1	
AS-i profile	M3	
Mechanical data		
Housing	housing for DIN rail mounting	
Materials	aluminium; steel sheet galvanised	
Displays / operating elements		
Display	function	3 x LED, red
		2 x LED, green
		2 x LED, yellow
		full graphic LCD display
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connection		

