




Boîtier de contrôle pour capteurs de débit

VS0100/ 24VDC

Cet article n'est plus disponible - entrée d'archives



Application		
Application		Surveillance du débit
Données électriques		
Tolérance de la tension d'alimentation	[%]	-10...10
Tension d'alimentation	[V]	24 DC
Consommation	[mA]	40; (24 V)
Nombre de voies		1
Sorties		
Technologie		relais
Fonction de commutation surveillance du débit		le relais est enclenché en cas de débit
Conditions d'utilisation		
Température ambiante	[°C]	-20...60
Indice de protection		IP 40
Protection bornes		IP 20
Données mécaniques		
Boîtier		montage sur rail
Dimensions	[mm]	75 x 55 x 110
Matières		plastique
Remarques		
Unité d'emballage		1 pièces

VS0100/ 24VDC

Bornes de raccordement: 16 x ...2,5 mm²

Figure 1: Pin connections for the 16-pin connector. The diagram shows two vertical columns of pins. The left column has pins 1 through 8, and the right column has pins 9 through 16. A 16-pin connector is shown on the left, with four lines labeled BN, YE, GN, and WH. BN is connected to pin 4, YE to pin 5, GN to pin 6, and WH to pin 7. Pin 10 is connected to pin 9. Pin 11 is connected to pin 10. Pin 13 is connected to ground (GND). Pin 15 is connected to L- 24V DC. Pin 16 is connected to L+.

1: Relais Surveillance du débit
Couleurs des fils conducteurs :
BN = brun
YE = jaune
GN = vert
WH = blanc