




AS-Interface ClassicLine module

ClassicLine 3DO T M12

Article no longer available - archive entry

Alternative articles: AC5203

When selecting an alternative article and accessories please note that technical data may differ!



- 1 panel for labelling
2 fixture infrared adapter



Electrical data

Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	50
Max. current load total	[A]	2
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 3
------------------------------	------------------------------

Outputs

Electrical design	AS-i
Number of digital outputs	3
Circuit	PNP
Voltage range DC	[V] 15...30; (to PELV)
Max. current load per output	[mA] 1000; (utilisation category DC-13 (control of electromagnets): 20 W (IEC 60947-5-1))
Short-circuit proof	yes
Electrically separated	yes

Operating conditions

Ambient temperature	[°C] -25...70
Protection	IP 67



AS-Interface ClassicLine module

ClassicLine 3DO T M12

Tests / approvals		
EMC	EN 50295	
AS-i classification		
AS-i version		2.1
Extended addressing mode		yes
AS-i profile		S-8.A.E
AS-i I/O configuration [hex]		8
AS-i ID code [hex]		A.E
Mechanical data		
Weight [g]		108.6
Type of mounting		AS-i interface to FC-E lower parts
Materials		PBT
Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow
Accessories		
Accessories (optional)		Module lower part
Remarks		
Pack quantity		1 pcs.
Electrical connection		
contact pins to module lower part, FK-E:		
Connector: M12; coding: A		
1	Outputs	
2	not used	
3	not used	
4	external voltage AUX -	
5	switching output +	
	not used	