


EVC471



Connecting cable with socket

ADOGH040MSS0001H04

Please see the technical note under "Downloads"



| Application | | | | | | | | | |
|-----------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------|--------------------------|--------------|------------------------------------------------------------------------------------------------|----------------|----------|------------------|-----------|
| Special feature | Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability | | | | | | | | |
| Application | Industrial applications / factory automation; Use in machine tools, coolants and lubricants | | | | | | | | |
| Free from silicone | yes | | | | | | | | |
| Electrical data | | | | | | | | | |
| Operating voltage [V] | < 250 AC / < 300 DC | | | | | | | | |
| Protection class | II | | | | | | | | |
| Max. current load total [A] | 4 | | | | | | | | |
| Operating conditions | | | | | | | | | |
| Ambient temperature [°C] | -25...90 | | | | | | | | |
| Note on ambient temperature | cULus: ...75 °C | | | | | | | | |
| Ambient temperature (moving) [°C] | -25...90 | | | | | | | | |
| Note on ambient temperature (moving) | cULus: ...75 °C | | | | | | | | |
| Storage temperature [°C] | -25...55 | | | | | | | | |
| Storage humidity [%] | 10...100 | | | | | | | | |
| Other climatic conditions for storage according to stated class | 1K22/ DIN 60721-3-1 | | | | | | | | |
| Protection | IP 65; IP 67; IP 68; IP 69K | | | | | | | | |
| Mechanical data | | | | | | | | | |
| Weight [g] | 48.2 | | | | | | | | |
| Dimensions [mm] | 15.5 x 15.5 x 45 | | | | | | | | |
| Moulded-body material | TPU | | | | | | | | |
| Material nut | brass, nickel-plated | | | | | | | | |
| Sealing material | FKM | | | | | | | | |
| Drag chain suitability | yes | | | | | | | | |
| Drag chain suitability | <table border="1"> <tr> <td>bending radius for flexible use</td> <td>min. 10 x cable diameter</td> </tr> <tr> <td>travel speed</td> <td>max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²</td> </tr> <tr> <td>bending cycles</td> <td>> 5 Mio.</td> </tr> <tr> <td>torsional strain</td> <td>± 180 °/m</td> </tr> </table> | bending radius for flexible use | min. 10 x cable diameter | travel speed | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ² | bending cycles | > 5 Mio. | torsional strain | ± 180 °/m |
| bending radius for flexible use | min. 10 x cable diameter | | | | | | | | |
| travel speed | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ² | | | | | | | | |
| bending cycles | > 5 Mio. | | | | | | | | |
| torsional strain | ± 180 °/m | | | | | | | | |
| Remarks | | | | | | | | | |
| Notes | Please see the technical note under "Downloads" | | | | | | | | |

EVC471



Connecting cable with socket

ADOGH040MSS0001H04

Pack quantity

1 pcs.

Electrical connection


Cable: 1 m, PUR, Halogen-free, black, Ø 4.3 mm; 4 x 0.34 mm²

Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Contacts: 4, gold-plated; Moulded body: TPU, orange; Locking: brass, nickel-plated; Sealing: FKM; Tightening torque: 0.6...1.5 Nm




Connection



Core colours :
BK = black
BN = brown
BU = blue
WH = white

Diagrams and graphs

characteristic line for derating



Derating $I_{max} * 0.8$ (DIN EN 60512-5-2)

X Ambient temperature [°C]

Y Current [A]