


Article no longer available - archive entry

Alternative articles: AC2024

When selecting an alternative article and accessories please note that technical data may differ!



- 1 tube connection Ø 8 mm
2 panel for labelling

**Electrical data**

Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 150
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 2; Number of pneumatic outputs: 2
------------------------------	---

Inputs

Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Power supply	[V]	20...30
Max. total current rating of inputs	[mA]	100
Input current High	[mA]	> 3
Input current Low	[mA]	< 1.5
Switching level high	[V]	> 10
Digital inputs protected against short circuits		yes



AS-Interface AirBox

AirBox 2DI 2PO M12

Outputs						
Electrical design	AS-i					
Number of pneumatic outputs	2					
Operating conditions						
Ambient temperature	[°C]	0...55				
Note on ambient temperature	with special compressed air treatment: < 0 °C					
Protection	IP 65					
Tests / approvals						
EMC	EN 50295					
AS-i classification						
AS-i profile	S-3.F					
AS-i I/O configuration	[hex]	3				
AS-i ID code	[hex]	F				
AS-i certificate	10501					
Assignment of the data bits	data bit	D0	D1	D2	D3	
	Inputs / outputs	I-1	I-2	O-3	O-4	
Mechanical data						
Type of mounting	screw mounting					
Materials	PBT					
Pneumatic system	2 x 3/2-way seat valves					
Operating pressure range	[bar]	2...8				
Operating pressure range	[MPa]	0.2...0.8				
Note on working pressure range	incl. possible pressure peaks					
Air flow at 6/5 bar	[l/min]	350				
Air flow at 6/0 bar	[l/min]	550				
Permissible compressed air	filtered (5 µm); lubricated (ISO-VG10) or not lubricated					
Tube fittings	Legris LF 3000/8					
Exhaust	integrated exhaust					
Displays / operating elements						
Display	operation				LED, green	
	function				LED, yellow	
Electrical connection						
Module connection	Flat cables					
Remarks						
Remarks	Please see the notes on compressed air and EMC/ESD under "Downloads"					
Pack quantity	1 pcs.					




AS-Interface AirBox

AirBox 2DI 2PO M12

Electrical connection

contact pins to module lower part, FK / PG:

Connector: M12; coding: A

A diagram of an M12 connector pinout. It shows a circular arrangement of five pins. Pin 1 is at the top, pin 2 is at the top-right, pin 3 is at the bottom-right, pin 4 is at the bottom, and pin 5 is at the top-left. A line connects pins 2 and 4, indicating they are internally bridged.

	Inputs
1	Sensor supply L+
2+4	data input internally bridged
3	Sensor supply L-