


# E11067



## Adapter socket

EDOGH040ZDS00,5E04 (PG9)



1 O-ring



### Application

Application: Industrial applications / factory automation

### Electrical data

Operating voltage [V]	< 250 AC/DC
Max. current load total [A]	4

### Operating conditions

Ambient temperature [°C]	-25...85
Protection	IP 68

### Mechanical data

Weight [g]	22.8
Mounting thread	PG 9
Materials	housing: diecast zinc

### Accessories

Items supplied: nut: 1 x PG9

### Remarks


Pack quantity: 1 pcs.

### Electrical connection

Cable: 0.5 m, PVC; 4 x 0.25 mm<sup>2</sup>

### Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Contacts: 4




# E11067



## Adapter socket

EDOGH040ZDS00,5E04 (PG9)

### Connection



Core colours :  
BK = black  
BN = brown  
BU = blue  
WH = white