


Fibre optic through-beam sensor

FE-00-P-V-M4

Article no longer available - archive entry

Alternative articles: E20059

When selecting an alternative article and accessories please note that technical data may differ!



Application

Function principle	Through-beam sensor
--------------------	---------------------

Detection zone

Range with fibre-optic amplifier type	OKF; OUF
---------------------------------------	----------

OKF

Range of fibre optics [mm]	120
----------------------------	-----

OUF

Range of fibre optics [mm]	120
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Version of sensing head	straight
Sensing head thread	M4
Sensing head length [mm]	15
Total length [mm]	600

E20117



Fibre optic through-beam sensor

FE-00-P-V-M4

Min. bending radius	[mm]	20
Materials	Adapter: PPE	
Fibre material	glass	
Fibre head material	stainless steel (303/1.4305)	
Fibre sheath material	PVC	
Remarks		
Pack quantity	1 pcs.	