


# IE5344



## Inductive sensor

IEBC003BASKG/0,3M/AS



Product characteristics	
Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	3
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 37
Electrical data	
Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10; (only in 3-wire operation)
Protection class	III
Reverse polarity protection	yes
Outputs	
Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	2.8
Minimum load current [mA]	2
Max. leakage current [mA]	0.5; (only in 2-wire operation)
Permanent current rating of switching output DC [mA]	100; (only in 2-wire operation)
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes
Detection zone	
Sensing range [mm]	3
Operating distance [mm]	0...2.4
Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of Sr]	1...15

# IE5344



## Inductive sensor

IEBC003BASKG/0,3M/AS

### Operating conditions

Ambient temperature	[°C]	0...60
Protection		IP 67

### Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	1517
UL approval	Ta	-25...80 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current
	File number UL	E174191

### Mechanical data

Weight	[g]	24.6
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 37
Thread designation		M8 x 1
Materials		housing: brass white bronze coated; sensing face: LCP

### Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

### Accessories

Items supplied		lock nuts: 2 x M8
----------------	--	-------------------

### Remarks

Pack quantity		1 pcs.
---------------	--	--------

### Electrical connection - plug

Cable: 0.3 m, PVC; 3 x 0.14 mm<sup>2</sup>

Connector: 1 x M8; coding: A; Contacts: 3; Locking: snap-fit

