




Inductive sensor

IFK3004-BPOG/HS-400-HPX

Article no longer available - archive entry



Product characteristics		
Electrical design		PNP
Sensing range	[mm]	4
Housing		threaded type
Dimensions	[mm]	M12 x 1
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Outputs		
Electrical design		PNP
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	300
Short-circuit protection		no
Overload protection		no
Detection zone		
Sensing range	[mm]	4
Sensing range adjustable		no
Real sensing range Sr	[mm]	4 ± 10 %
Operating distance	[mm]	0...3.25



Inductive sensor

IFK3004-BPOG/HS-400-HPX

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M12 x 1
Thread designation		M12 x 1
Materials		brass nickel-plated; PBT
Accessories		
Items supplied		lock nuts: 2
Electrical connection		
Connection		

