
Fail-safe inductive sensor

GIFK4004-2PO/SIL2/US







	PNP	
	2 x OSSD (A1 and A2)	
[mm]	> 6	
	threaded type	
[mm]	M12 x 1 / L = 60	
	Gold-plated contacts	
	permanent operation	
	safe state when damped correctly	
	Use in mobile and harsh applications	
[V]	832 DC	
[V]	60	
[mA]	< 20	
	III	
	yes	
[ms]	1000	
	PNP	
	2 x OSSD (A1 and A2)	
[V]	2.5; (30 mA)	
[mA]	1	
[mA]	50	
[Hz]	10	
	Interface type C class 1	
	compatible with EN 61131-2 inputs type 1, 2	
	yes	
	yes	
[nF]	20	
	[mm] [V] [mA] [mA] [mA] [mA]	

Fail-safe inductive sensor



GIFK4004-2PO/SIL2/US

Detection zone				
Enable zone	[mm]	> 6		
Safe switch-off distance s(ao)	[mm]	< 3		
Accuracy / deviations				
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3		
Hysteresis [%	of Sr]	110		
Response times				
Response time to safety request	[ms]	5		
Response time when approaching the enable zone	[ms]	5		
Risk time (response time for safety-related faults)	[ms]	100		
Operating conditions				
Ambient temperature	[°C]	-4085		
Max. relative air humidity	[%]	50; (70 °C; <70 °C: >50 %)		
Max. height above sea level	[m]	5000		
Ionising radiation		not permissible		
Protection		IP 65; IP 67; IP 68; IP 69K; (with ifm socket duly screwed on)		

Fail-safe inductive sensor

GIFK4004-2PO/SIL2/US

Chemical media



test according to ISO 16750-5		
the following media were tested for 22 hours at 60 °C	coolants	
	(HoughtonHocut4480	
	Oemeta	
	HYCUT ET 46)	
The following media were tested for 22 hours at 75 $^{\circ}\text{C}$	hydraulic fluids	
	(Fuchs Renoling B15 VG 46 HLP	
	Total BiohydranTMP 4HEES	
	Fuchs Hydrotherm 46 M HFC)	
	transmission oils	
	(Fuchs TITAN ATF 3353 Dexron III)	
	diesel	
	biodiesel	
	urea	
	(AdBlue)	
	brake fluid	
	(K2 TURBO DOT 4)	
the following media were tested for 22 hours at 23 $^{\circ}\text{C}$	corrosion protection	
	(Sonax special preservation wax)	
	cold cleaner	
	(Sonax cold cleaner S)	
	ammonia-based cleaner	
	(Weco Dr. Webers Salmiak-Konzentrat (concentrated ammonium chloride))	
	battery acid	
the following media were tested for 2 hours at 23 °C	wheel rim cleaner	
	(Sonax Xtreme Plus)	
the following media were tested for 10 minutes at 23 °C	premium-grade petrol lead-free	

Fail-safe inductive sensor





Tests / approvals				
EMC		industrial environments		
		EN 60947-5-3		
		EN 61000-4-2 ESD	6 kV CD / 8 kV AD	
		EN 61000-4-3 HF radiated	20 V/m	
		EN 61000-4-4 Burst	2 kV	
		EN 61000-4-5 Surge	2 kV	
		EN 61000-4-6 HF conducted	10 V	
		EN 61000-4-8	30 A/m 50/60 Hz / 1000 A/m 0 Hz	
		EN 55011	class B	
		mobile applications	only for operation with central load-dump suppression (58 V) / not for active operation during motor start phase in 12 V systems	
		ISO 10605 ESD	8 kV CD / 15 kV AD	
		ISO 11452-2, ISO 11452-5 radiated immunity	100 V/m	
		ISO 7637-2, ISO 16750-2 conducted immunity	12 V / 24 V	
		pulse	1 2a 3a 3b 4 5b	
		severity level	III III III III III 58V	
		failure criterion	в в в А А С/В А	
		EN 55025		
Vibration resistance		EN 60068-2-6 Fc	20 g (103000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes	
Broadband noise		EN 60068-2-64 h	5,9 g (102000 Hz) / effective acceleration for chassis mounting	
Shock resistance		EN 60068-2-27 Ea	100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes	
Continuous shock resistance		EN 60068-2-27 Ea	40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes	
Fast temperature change		EN 60068-2-14 Na	TA = -40°C; TB = 85°C; t1 = 30 min; t2 = 10 s 100 cycles	
Salt spray test		EN 60068-2-52 Kb	severity level 5 (4 test cycles)	
Safety classification				
Complies with the		ISO 13849-1: 201	L5 category 2, PL d	
requirements			508 SIL 2	
•		IEC 62061 SIL 2		
Mission time TM	[h]	≤ 87600		
Mission time TM (additional indication)		industrial environments Temperature range -2570 °C ≤ 175200		
PFH	[1/h]	< 5E-08		
Mechanical data				
Weight	[g]	0	6.0	
_	[9]	86.8		
Housing		threaded type		
Mounting		non-flush mountable		
Dimensions	[mm]	M12 x 1 / L = 60		
Thread designation		M1	2 x 1	
Materials		threaded sleeve: brass white bronze coated; sensing face: LCP; LED window: PEI; lock nuts: brass white bronze coated		
Tightening torque	[Nm]	< 7		

Fail-safe inductive sensor






Displays / operating elements					
Display	Display switching status	4 LED, yellow			
Accessories					
Items supplied		lock nuts: 2			
Remarks					
Remarks	material for secure mount	material for secure mounting not supplied; fixing must be done by the user			
		meets the environmental and EMC requirements for operation in agricultural and forestry machinery, earthworks and construction machines as well as in industrial trucks			
		When used in industrial trucks, the screen of the connection cable has to be connected to the sensor.			
		Unless stated otherwise, all data refer to the reference target plate to IEC 60947-5-2 over the whole temperature range.			
	(FE3	(FE360 = ST37-2K) 12x12x1 mm			
Pack quantity		1 pcs.			

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



1: safety-related logic unit