

Inductive sensor

IEB3001-BPKG/PH



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 35

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	10; (24 V)
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	750
Notes on switching frequency [Hz]	1000 nb
Short-circuit protection	yes
Overload protection	yes

Detection zone

Sensing range [mm]	1
Real sensing range S_r [mm]	$1 \pm 10 \%$
Operating distance [mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of S_r]	3...15
Switch point drift [% of S_r]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

IE5199



Inductive sensor

IEB3001-BPKG/PH

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
MTTF	[years]	2804

Mechanical data		
Weight	[g]	47
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 35
Thread designation		M8 x 1
Materials		brass nickel-plated; PBT
Tightening torque	[Nm]	A = 5 mm: 1 Nm; B: 2 Nm


Displays / operating elements		
Display	switching status	1 x LED, yellow

Accessories		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

Electrical connection		
Cable: 2 m, PUR; highly flexible; 3 x 0.14 mm ²		

Connection		
------------	--	--



	Core colours :
BK =	black
BN =	brown
BU =	blue

IE5199

Inductive sensor

IEB3001-BPKG/PH



Diagrams and graphs

Installation

