


Capacitive sensor

KNM30BSAAPKG/US

Article no longer available - archive entry



1 programming button



Product characteristics

Electrical design	PNP
Output function	normally closed
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 100

Application

Special feature	Function check output
Installation	flush mounting in tank wall
Media	dry bulk material
Medium temperature [°C]	-25...80

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	30; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Function check output	yes
Max. voltage drop of function check output [V]	3.5
Max. current load for function check output [mA]	10
Permanent current rating of switching output DC [mA]	250

KN5125



Capacitive sensor

KNM30BSAAPKG/US

Switching frequency DC	[Hz]	5
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

Mechanical data

Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 100
Thread designation		M30 x 1.5
Materials		brass white bronze coated; PBT

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A




KN5125



Capacitive sensor

KNM30BSAAPKG/US

Connection



2: Function check output programming wire