


Inductive sensor

IIA3015-APKG/BS-301-APO

Article no longer available - archive entry

Alternative articles: IIS209

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	15
Housing	threaded type
Dimensions [mm]	M30 x 1.5

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	200
Short-circuit protection	yes

**Inductive sensor**

IIA3015-APKG/BS-301-APO

Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone	
Sensing range [mm]	15
Real sensing range S_r [mm]	$15 \pm 10 \%$
Operating distance [mm]	0...12.1

Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [% of S_r]	1...15
Switch point drift [% of S_r]	-10...10

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 65

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data	
Housing	threaded type
Mounting	non-flush mountable
Dimensions [mm]	M30 x 1.5
Thread designation	M30 x 1.5
Materials	brass nickel-plated; CO-PC

Displays / operating elements		
Display	switching status	1 x LED, yellow

Accessories	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x M18; coding: A





Inductive sensor

IIA3015-APKG/BS-301-APO

Connection

