


# IM5132



## Inductive sensor

IMC4020BCPKG/K1/US-100-DPA



- 1 LED yellow
- 2 LED green



### Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	20
Housing	rectangular
Dimensions [mm]	40 x 40 x 54

### Application

Special feature	Correction factor K = 1; Magnetic-field immune
Magnetic-field immune	yes
Max. magnetic field immunity [mT]	300

### Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 20
Protection class	II
Reverse polarity protection	yes

### Outputs

Electrical design	PNP
Output function	complementary
Max. voltage drop switching output DC [V]	2.5
Max. leakage current [mA]	0.1

# IM5132



## Inductive sensor

IMC4020BCPKG/K1/US-100-DPA

Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	200
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

<b>Detection zone</b>		
Sensing range [mm]		20
Real sensing range Sr [mm]		20 ± 10 %
Operating distance [mm]		0...16.2

<b>Accuracy / deviations</b>		
Correction factor		steel: 1 / stainless steel: 1 / brass: 1 / aluminium: 1 / copper: 1
Hysteresis [% of Sr]		1...20
Switch point drift [% of Sr]		-10...10
Correction factor K = 1		yes

<b>Operating conditions</b>		
Ambient temperature [°C]		-25...70
Protection		IP 67; IP 69K

<b>Tests / approvals</b>		
EMC	EN 61000-4-2 ESD	8 kV CD / 6 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF [years]		975
UL approval	Ta	-25...70 °C
	Enclosure type	Type 1
	power supply	Class 2
	File number UL	E174191

<b>Mechanical data</b>		
Weight [g]		141.5
Housing		rectangular
Sensing face		5 positions selectable
Mounting		flush mountable
Dimensions [mm]		40 x 40 x 54
Materials		housing: PA; sensing face: PA black; bevelled housing part: PA; clamp: orange; screw: stainless steel (304CU/1.4567)

<b>Displays / operating elements</b>		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green

<b>Remarks</b>		
Pack quantity		1 pcs.

# IM5132



## Inductive sensor

IMC4020BCPKG/K1/US-100-DPA

### Electrical connection - plug

Connector: 1 x M12; coding: A; Locking: locking, rotatable, stainless steel (316L/1.4404)



### Connection

