IV5050

Inductive sensor

IVE4020ZCPKG

Article no longer available - archive entry

Alternative articles: IV5053

When selecting an alternative article and accessories please note that technical data may differ!



CE

Product characteristics		
Electrical design		PNP
Output function		complementary
Sensing range	[mm]	20
Housing		rectangular
Dimensions	[mm]	40 x 40 x 118
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	20; (24 V)
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		complementary
Max. voltage drop switching output DC	[V]	3

IV5050

Inductive sensor

IVE4020ZCPKG

Permanent current rating of switching output DC	[mA]	200	
Switching frequency DC	[Hz]	150	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Detection zone			
Sensing range	[mm]	20	
Real sensing range Sr	[mm]	20 ± 10 %	
Operating distance	[mm]	0...16.2	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15	
Switch point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...100	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		rectangular	
Mounting		flush mountable	
Dimensions	[mm]	40 x 40 x 118	
Materials		PBT; Sealing: FKM	
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Remarks		5 positions of the active zone possible	
		Cable gland (E11270) to be ordered separately	
Pack quantity		1 pcs.	

IV5050

Inductive sensor

IVE4020ZCPKG

Electrical connection

terminals: ...2.5 mm²

Connection