

O7P203



Retro-reflective sensor


O7P-HNKG/0,20M/AS

phase-out article

Discontinuation date: 03/31/2026

Alternative articles: O7P201

When selecting an alternative article and accessories please note that technical data may differ!



receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	red light
Housing	rectangular

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor
Application	For applications in robotics, assembly and handling technology

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	20; ((24 V))
Protection class	III
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	633

Outputs

Electrical design	NPN
Output function	light-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	1000
Short-circuit protection	yes

O7P203



Retro-reflective sensor

O7P-HNKG/0,20M/AS

Type of short-circuit protection	pulsed
----------------------------------	--------

Detection zone	
Range referred to prismatic reflector [m]	0.03...1; (Prismatic reflector Ø 80 E20005; Prismatic reflector 50 x 50 mm E21299)
Range adjustable	no
Max. light spot diameter [mm]	55
Light spot dimensions refer to	at maximum range
Polarisation filter available	yes

Operating conditions	
Ambient temperature [°C]	-25...60
Protection	IP 65

Tests / approvals	
EMC	EN 60947-5-2
MTTF [years]	969

Mechanical data	
Weight [g]	14.4
Housing	rectangular
Dimensions [mm]	20.3 x 15 x 9
Materials	housing: PA
Lens material	front pane:PMMA
Lens alignment	side lens
Tightening torque [Nm]	0.5

Displays / operating elements	
Display	switching status 1 x LED, yellow

Remarks	
Remarks	operating voltage "supply class 2" according to UL
Pack quantity	1 pcs.

Electrical connection

Cable: 0.2 m, PUR; 3 x 0.14 mm²

Connector: 1 x M8; coding: A; Contacts: 3; Locking: snap-fit



O7P203



Retro-reflective sensor

O7P-HNKG/0,20M/AS

Connection

