


KF5001



Capacitive sensor

KFA3040BBPKG/NI/US



- 1 LED 4 x 90°
- 2 potentiometer



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1...6
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 60

Application

Media	dry bulk material; liquids
-------	----------------------------

Electrical data

Operating voltage [V]	10...36 DC; ("supply class 2" to cULus)
Current consumption [mA]	< 12
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	50
Short-circuit proof	yes
Overload protection	yes

Detection zone

Sensing range [mm]	1...6
Sensing range adjustable	yes
Factory setting sensing range [mm]	4
Real sensing range Sr [mm]	4 ± 10 %

Accuracy / deviations

Correction factor	glass: 0.6 / water: 1 / ceramics: 0.5 / PVC: 0.4
Hysteresis [% of Sr]	1...15

KF5001



Capacitive sensor

KFA3040BBPKG/NI/US

Switch point drift	[% of Sr]	-20...20
--------------------	-----------	----------

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 65
Increased immunity		yes

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[years]	636

Mechanical data

Weight	[g]	39.3
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M12 x 1 / L = 60
Thread designation		M12 x 1
Materials		stainless steel (1.4404 / 316L); PEEK

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories


Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A



Connection

