


# LR9020



## Continuous level sensor (guided wave radar)

LR0000--BR34A1DKG/US



- 1 Sealing  
A active range  
I1 / I2 inactive ranges



### Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1	
Probe length L [mm]	100...1600	
Process connection	G 3/4 external thread	
<b>Application</b>		
Special feature	Gold-plated contacts	
Media	hydrous coolants; oils; oil-based media; water; media similar to water	
Dielectric constant of the medium	$\geq 2$ ; (for media with a dielectric constant of 2...20 (e.g. oils), a coaxial pipe is needed for operation)	
Conditionally suitable for	See the operating instructions, chapter "Function and features".	
Medium temperature [°C]	0...80; (90 < 1 h)	
Tank pressure [bar]	-1...16	
MAWP (for applications according to CRN) [bar]	25	

### Electrical data

Operating voltage [V]	18...30 DC
Current consumption [mA]	< 80
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	< 3

# LR9020



## Continuous level sensor (guided wave radar)

LR0000--BR34A1DKG/US

Measuring principle	guided wave radar				
<b>Inputs / outputs</b>					
Number of inputs and outputs	Number of analogue outputs: 1				
<b>Outputs</b>					
Total number of outputs	1				
Output signal	analogue signal; IO-Link				
Number of analogue outputs	1				
Analogue current output [mA]	4...20				
Max. load [Ω]	500				
Analogue voltage output [V]	0...10				
Min. load resistance [Ω]	2000				
Overload protection	yes				
<b>Measuring/setting range</b>					
Probe length L [mm]	100...1600				
Active range A [mm]	L-40 (L-60); (when set to oil and oil based media)				
Inactive range I1 / I2 [mm]	30 / 10 (30); (when set to oil and oil based media)				
<b>Accuracy / deviations</b>					
Repeatability [mm]	± 5				
Switch point accuracy [mm]	± (15 + 0,5 % ); (% of the final value of the measuring range: L - 30 mm)				
Offset error [mm]	10				
Measuring sensitivity	16 mA ÷ MEW 10 V ÷ MEW				
Resolution [mm]	0,5 (L < 300 mm) 0,2% MEW (L > 300 mm)				
Zero signal (voltage) [V]	0...0.2				
Zero signal (current) [mA]	3.95...4.0				
Full signal (voltage) [V]	10...10.1				
Full signal (current) [mA]	20...20.2				
Characteristics deviation	± 10				
<b>Interfaces</b>					
Communication interface	IO-Link				
Transmission type	COM2 (38,4 kBaud)				
IO-Link revision	1.1				
SDCI standard	IEC 61131-9 CDV				
Profiles	no profile				
SIO mode	no				
Required master port type	A				
Process data analogue	1				
Min. process cycle time [ms]	2.3				
Supported DeviceIDs	<table border="1"> <thead> <tr> <th>Type of operation</th><th>DeviceID</th></tr> </thead> <tbody> <tr> <td>default</td><td>578</td></tr> </tbody> </table>	Type of operation	DeviceID	default	578
Type of operation	DeviceID				
default	578				
<b>Operating conditions</b>					
Ambient temperature [°C]	0...60				
Storage temperature [°C]	-25...80				

# LR9020



## Continuous level sensor (guided wave radar)

LR0000--BR34A1DKG/US

Protection

IP 68; IP 69K

### Tests / approvals

EMC	EN 61000-6-2	
	EN 61000-6-3	in a metal tank
	EN 61000-6-4	in a plastic tank
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)
MTTF [years]		239

### Mechanical data

Weight [g]	470.9
Materials	stainless steel (304/1.4301); stainless steel (316L/1.4404); FKM; PEI
Materials (wetted parts)	stainless steel (303/1.4305); probe connection: stainless steel (316L/1.4435); PTFE; FKM; Sealing: NBR reinforced fibre
Process connection	G 3/4 external thread

### Remarks


Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



OUT1: IO-Link

OUT2: analogue output  
colours to DIN EN 60947-5-2

Core colours :

BK = black

BN = brown

BU = blue

WH = white