


O8P203



Retro-reflective sensor

O8P-DNKG/0,30M/AS/3P



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Special feature		polarisation filter
Function principle		Retro-reflective sensor
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	20; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	633
Outputs		
Electrical design		NPN
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5

O8P203



Retro-reflective sensor

O8P-DNKG/0,30M/AS/3P

Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	pulsed

Detection zone	
Range referred to prismatic reflector [m]	0.02...1.8; (Prismatic reflector Ø 30 E20004)
Range adjustable	no
Max. light spot diameter [mm]	120
Light spot dimensions refer to	at maximum range
Polarisation filter available	yes


Operating conditions	
Ambient temperature [°C]	-25...60
Protection	IP 65; IP 67

Tests / approvals		
EMC	EN 60947-5-2	
MTTF [years]	1067	
UL approval	Ta	-25...60 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current
	UL approval no.	E015
	File number UL	E174191

Mechanical data	
Weight [g]	21.2
Housing	rectangular
Dimensions [mm]	28.1 x 8.1 x 14.4
Materials	housing: ABS; rear of the housing: stainless steel (316L/1.4404)
Lens material	front pane:PMMA
Lens alignment	side lens

Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Remarks	
Pack quantity	1 pcs.


Electrical connection	
Cable: 0.3 m, PVC, black, Ø 2.9 mm; 3 x 0.08 mm ²	
Connector: 1 x M8; coding: A	
	



Retro-reflective sensor


O8P-DNKG/0,30M/AS/3P

Connection



Diagrams and graphs

excess gain graph



x: distance [mm]

y: excess gain factor