

OH5015




Through-beam sensor receiver

OHE-DPKG/0,20M/AS

Article no longer available - archive entry

Alternative articles: O8E202

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Type of light	red light
Housing	rectangular
Dimensions [mm]	25.1 x 7.6 x 12.5

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	660

Outputs


Electrical design	PNP
Output function	dark-on mode
Permanent current rating of switching output DC [mA]	50
Switching frequency DC [Hz]	200
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

OH5015



Through-beam sensor receiver

OHE-DPKG/0,20M/AS

Detection zone		
Transmitter / receiver		receiver
Range [m]		< 1.2
Range adjustable		no
Response times		
Response time [s]		< 2.5
Operating conditions		
Ambient temperature [°C]		-20...50
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Weight [g]		14.8
Housing		rectangular
Dimensions [mm]		25.1 x 7.6 x 12.5
Materials		ABS
Lens material		PMMA
Lens alignment		side lens
Displays / operating elements		
Display	switching status	1 x LED, yellow
	unsafe zone	1 x LED, yellow flashing
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 0.2 m, PVC		
Connector: 1 x M8		
		

OH5015



Through-beam sensor receiver

OHE-DPKG/0,20M/AS

Connection

