


Retro-reflective laser sensor

OJR-DPKG/SO/AS

phase-out article

Alternative articles: O6P202

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Type of light	red light
Housing	rectangular

Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 20
Protection class	III
Reverse polarity protection	yes
Type of light	red light

Outputs

Electrical design	PNP
Output function	dark-on mode
Max. voltage drop switching output DC [V]	2.5



Retro-reflective laser sensor

OJR-DPKG/SO/AS

Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Range referred to prismatic reflector [m]	1.8; (Prismatic reflector Ø 80 E20005)
Range adjustable	no
Max. light spot diameter [mm]	64
Light spot dimensions refer to	at maximum range

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2
MTTF [years]	905

Mechanical data

Weight [g]	15.5
Housing	rectangular
Dimensions [mm]	35 x 11 x 24
Materials	ABS; SEPS
Lens material	PMMA
Lens alignment	side lens

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Remarks	operating voltage "supply class 2" according to cULus
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M8; coding: A





Retro-reflective laser sensor

OJR-DPKG/SO/AS

Connection

