

PN2292



Pressure sensor with display

PN-100-SEN14-MFRKG/US/ IV



- 1 alphanumeric display 4-digit red/green
- 2 LEDs Display unit / switching status
- 3 programming button
- 4 upper part of the housing can be rotated 345°



Product characteristics

| | | | |
|------------------------------|---|--------------|------------|
| Number of inputs and outputs | Number of digital outputs: 2; Number of analogue outputs: 1 | | |
| Measuring range | 0...100 bar | 0...1450 psi | 0...10 MPa |
| Process connection | threaded connection 1/4" NPT internal thread | | |

Application

| | | | |
|--|--|----------|--------|
| Special feature | Gold-plated contacts | | |
| Measuring element | ceramic-capacitive pressure measuring cell | | |
| Application | for industrial applications | | |
| Media | Liquids | | |
| Conditionally suitable for | use in gases at pressures > 25 bar only on request | | |
| Medium temperature [°C] | -25...80 | | |
| Min. burst pressure | 650 bar | 9400 psi | 65 MPa |
| Pressure rating | 300 bar | 4350 psi | 30 MPa |
| Vacuum resistance | -1000 mbar | -0.1 MPa | |
| Type of pressure | relative pressure | | |
| MAWP for applications according to CRN [bar] | 125 | | |

Electrical data

| | | | |
|---------------------------------|----------------------------|--|--|
| Operating voltage [V] | 18...30 DC; (to SELV/PELV) | | |
| Current consumption [mA] | < 35 | | |
| Min. insulation resistance [MΩ] | 100; (500 V DC) | | |

PN2292



Pressure sensor with display

PN-100-SEN14-MFRKG/US/ IV

| | |
|-----------------------------|-----|
| Protection class | III |
| Reverse polarity protection | yes |
| Power-on delay time [s] | 0.3 |
| Integrated watchdog | yes |

Inputs / outputs

| | |
|------------------------------|---|
| Number of inputs and outputs | Number of digital outputs: 2; Number of analogue outputs: 1 |
|------------------------------|---|

Outputs

| | |
|--|--|
| Total number of outputs | 2 |
| Output signal | switching signal; analogue signal; IO-Link; (configurable) |
| Electrical design | PNP/NPN |
| Number of digital outputs | 2 |
| Output function | normally open / normally closed; (parameterisable) |
| Max. voltage drop switching output DC [V] | 2 |
| Permanent current rating of switching output DC [mA] | 250 |
| Switching frequency DC [Hz] | < 500 |
| Number of analogue outputs | 1 |
| Analogue current output [mA] | 4...20; (scalable 1:5) |
| Max. load [Ω] | 500 |
| Analogue voltage output [V] | 0...10; (scalable 1:5) |
| Min. load resistance [Ω] | 2000 |
| Short-circuit protection | yes |
| Type of short-circuit protection | pulsed |
| Overload protection | yes |

Measuring/setting range

| | | | |
|----------------------|--------------|----------------|------------|
| Measuring range | 0...100 bar | 0...1450 psi | 0...10 MPa |
| Analogue start point | 0...80 bar | 0...1160 psi | 0...8 MPa |
| Analogue end point | 20...100 bar | 290...1450 psi | 2...10 MPa |

Factory setting / CMPT = 2

| | | | |
|-----------------------------------|----------------|---------------|-----------------|
| Set point SP | 0.6...100 bar | 10...1450 psi | 0.06...10 MPa |
| Reset point rP | 0.2...99.6 bar | 4...1444 psi | 0.02...9.96 MPa |
| Min. difference between SP and rP | 0.6 bar | 6 psi | 0.06 MPa |
| In steps of | 0.2 bar | 2 psi | 0.02 MPa |

Status_B High Resolution / CMPT = 3

| | | | |
|-----------------------------------|----------------|--------------|-----------------|
| Set point SP | 0.6...100 bar | 9...1450 psi | 0.06...10 MPa |
| Reset point rP | 0.2...99.6 bar | 3...1444 psi | 0.02...9.96 MPa |
| Min. difference between SP and rP | 0.5 bar | 6 psi | 0.05 MPa |
| In steps of | 0.1 bar | 1 psi | 0.01 MPa |

Accuracy / deviations

| | |
|---------------------------------------|--|
| Switch point accuracy [% of the span] | < ± 0,4; (Turn down 1:1) |
| Repeatability [% of the span] | < ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1) |

PN2292



Pressure sensor with display

PN-100-SEN14-MFRKG/US/ IV

| | |
|--|--|
| Characteristics deviation [% of the span] | $< \pm 0,25$ (BFSL) / $< \pm 0,5$ (LS); (Turn down 1:1; BFSL = Best Fit Straight Line; LS = limit value setting) |
| Hysteresis deviation [% of the span] | $< \pm 0,1$; (Turn down 1:1) |
| Long-term stability [% of the span] | $< \pm 0,05$; (Turn down 1:1; per 6 months) |
| Temperature coefficient zero point [% of the span / 10 K] | $< \pm 0,2$; (-0...80 °C) |
| Temperature coefficient span [% of the span / 10 K] | $< \pm 0,2$; (-0...80 °C) |
| Notes on the accuracy / deviation | switch point accuracy, linearity error under DNV GL: $< \pm 1\%$; $< \pm 1\%$ |

Response times

| | |
|---|---------|
| Response time [ms] | < 1.5 |
| Delay time programmable dS, dr [s] | 0...50 |
| Damping process value dAP [s] | 0...4 |
| Damping for the analogue output dAA [s] | 0...4 |
| Max. response time analogue output [ms] | 3 |

Software / programming

| | |
|---------------------------|--|
| Parameter setting options | hysteresis / window; normally open / normally closed; switch-on/ switch-off delay; Damping; Display unit; current/voltage output |
|---------------------------|--|

Interfaces

| Communication interface | IO-Link | | | | | | |
|-------------------------------------|--|-------------------|----------|----------------------------|-----|-------------------------------------|-----|
| Transmission type | COM2 (38,4 kBaud) | | | | | | |
| IO-Link revision | 1.1 | | | | | | |
| SDCI standard | IEC 61131-9 | | | | | | |
| SIO mode | yes | | | | | | |
| Required master port type | A; (when pin 2 not connected: B) | | | | | | |
| Supported DeviceIDs | <table border="1"> <thead> <tr> <th>Type of operation</th> <th>DeviceID</th> </tr> </thead> <tbody> <tr> <td>Factory setting / CMPT = 2</td> <td>471</td> </tr> <tr> <td>Status_B High Resolution / CMPT = 3</td> <td>987</td> </tr> </tbody> </table> | Type of operation | DeviceID | Factory setting / CMPT = 2 | 471 | Status_B High Resolution / CMPT = 3 | 987 |
| Type of operation | DeviceID | | | | | | |
| Factory setting / CMPT = 2 | 471 | | | | | | |
| Status_B High Resolution / CMPT = 3 | 987 | | | | | | |
| Note | For further information please see the IODD PDF file under "Downloads" | | | | | | |

Factory setting / CMPT = 2

| | | |
|-----------------------------------|------------------------------|-------------------------|
| Profiles | Smart Sensor - SSP 0 | Generic Profiled Sensor |
| | Function | Device identification |
| | Function | Process data variable |
| | Function | Device diagnosis |
| Min. process cycle time [ms] | 2.3 | |
| IO-Link resolution pressure [bar] | 0.1 | |
| IO-Link process data (cyclical) | function | bit length |
| | pressure | 14 |
| | binary switching information | 2 |
| IO-Link functions (acyclical) | application specific tag | |

PN2292



Pressure sensor with display

PN-100-SEN14-MFRKG/US/ IV

| Status_B High Resolution / CMPT = 3 | | |
|---|---|--|
| Profiles | Smart Sensor - SSP 3.1 Common - I&D | Measuring Sensor Identification and Diagnosis |
| Min. process cycle time [ms] | | 3 |
| IO-Link resolution pressure [bar] | | 0.05 |
| IO-Link process data (cyclical) | function | bit length |
| | pressure | 16 |
| | device status | 4 |
| | binary switching information | 2 |
| IO-Link functions (acyclical) | application specific tag | |
| Operating conditions | | |
| Ambient temperature [°C] | | -25...80 |
| Storage temperature [°C] | | -40...100 |
| Protection | | IP 65; IP 67 |
| Tests / approvals | | |
| EMC | DIN EN 61000-6-2 | |
| | DIN EN 61000-6-3 | |
| Shock resistance | DIN EN 60068-2-27 | 50 g (11 ms) |
| Vibration resistance | DIN EN 60068-2-6 | 20 g (10...2000 Hz) |
| MTTF [years] | | 138 |
| UL approval | UL approval no. | J013 |
| Pressure Equipment Directive | Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request | |
| Mechanical data | | |
| Weight [g] | | 261 |
| Housing | | cylindrical |
| Dimensions [mm] | | Ø 34 / L = 90.7 |
| Materials | stainless steel (316L/1.4404); PBT+PC-GF30; PBT-GF20; PC | |
| Materials (wetted parts) | stainless steel (316L/1.4404); Al2O3 (96%; ceramics); FKM | |
| Min. pressure cycles | | 100 million |
| Tightening torque [Nm] | | > 50 |
| Process connection | | threaded connection 1/4" NPT internal thread |
| Restrictor element integrated | | no (can be retrofitted) |
| Displays / operating elements | | |
| Display | Display unit | 3 x LED, green (bar, psi, MPa) |
| | switching status | 2 x LED, yellow |
| | measured values | alphanumeric display, red/green 4-digit |
| Remarks | | |
| Pack quantity | | 1 pcs. |
| Electrical connection | | |
| Connector: 1 x M12; coding: A; Contacts: 4, gold-plated | | |
| | | |

PN2292



Pressure sensor with display

PN-100-SEN14-MFRKG/US/ /V

Connection



| | |
|------|------------------|
| OUT1 | switching output |
| | IO-Link |
| OUT2 | switching output |
| | analogue output |
| | Core colours : |
| BK = | black |
| BN = | brown |
| BU = | blue |
| WH = | white |