

OYA1210-20-4-20-P-1

Technical drawing of a 12V/20Ah battery, showing front, side, and detail views with dimensions in mm.

Front View (Left): Shows the battery terminals (T) and a label (1) with a warning symbol.

Side View (Top): Shows the battery terminals (R) and dimensions: 11 mm (terminal height), 61,5 mm (total height), 29,5 mm (terminal base height), and M12x1 (terminal thread).

Side View (Bottom): Shows the battery terminals (R) and dimensions: 11 mm (terminal height), 61,5 mm (total height), 29,5 mm (terminal base height), and M12x1 (terminal thread).

Top View (Right): Shows the battery terminals (R) and dimensions: 14,5 mm (terminal width), M5 (terminal thread), 1,5 mm (terminal base width), 40 mm (total width), 20 mm (terminal base width), and 10 mm (terminal base height).

Bottom View (Left): Shows the battery terminals (R) and dimensions: 30 mm (total width), 28 mm (terminal base width), and 10 mm (terminal base height).

Bottom View (Right): Shows the battery terminals (R) and dimensions: 28 mm (total width), 3 mm (terminal base width), 10,5 mm (terminal base height), 10 mm (terminal base width), and Ø5,5 (terminal base diameter).

- | | |
|---|---------------------------------------|
| T | transmitter |
| R | receiver |
| 1 | LED three-colour red / green / orange |
| 2 | LED 2-colour yellow/blue |
| 3 | LED 2-colour red/green |



Type of light	infrared light
Electrical design	PNP
Protection	IP 65; IP 67

Protective function	access prevention hand protection
---------------------	-----------------------------------



Safety light curtain

OYA1210-20-4-20-P-1

Electrical data		
Operating voltage tolerance	[%]	20
Operating voltage	[V]	24 DC
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 2
Type of light		infrared light
Wave length	[nm]	950
Receiver		
Current consumption	[mA]	83
Transmitter		
Current consumption	[mA]	42
Outputs		
Electrical design		PNP
Number of OSSD outputs		2
Max. current load per OSSD output	[mA]	400; (24 V)
Short-circuit protection		yes
Detection zone		
Protected area height	[mm]	1210
Resolution (detection capacity d)	[mm]	20
Protection area width (low light intensity)	[m]	0...10
Protection area width (high light intensity)	[m]	3...20
Response times		
Response time	[ms]	16.5
Operating conditions		
Applications		class C to EN 60654-1 weatherproof application
Ambient temperature	[°C]	-10...55
Max. relative air humidity	[%]	95
Protection		IP 65; IP 67
Tests / approvals		
EMC	IEC 61496-1	
Shock resistance	IEC 61496-1	
Vibration resistance	IEC 61496-1	
Safety classification		
ESPE type (IEC 61496-1)		4
Complies with the requirements		ISO 13849-1: 2015 category 4, PL e
		IEC 61508 SIL 3
		IEC 62061 SIL 3
Mission time TM	[h]	175200
PFH	[1/h]	2,7E-08

OY228S



Safety light curtain

OYA1210-20-4-20-P-1


Mechanical data		
Weight	[g]	4165
Dimensions	[mm]	1263 x 28 x 30
Materials		housing: aluminium; front pane: PC
Length L	[mm]	1263
Displays / operating elements		
Display		LED, yellow
		LED, green
		LED, red
		LED, blue
		LED, orange
Accessories		
Items supplied		mounting bracket: 6
		slot nuts: 6
		Nuts
Remarks		
Pack quantity		1 pcs.

Electrical connection - receiver

Connector: 1 x M12; coding: A; Maximum cable length: 100 m; for wire cross-section 0.34 mm²



Connection




Safety light curtain

OYA1210-20-4-20-P-1

Electrical connection - transmitter

Connector: 1 x M12; coding: A



Connection

