

PM2054




Flush pressure transmitter

PM-010-RES30-E-ZVG/US/ /P

phase-out article
Discontinuation date: 03/31/2024

Alternative articles: PI1004 or PM1704
When selecting an alternative article and accessories please note that technical data may differ!

Please do not use for new projects.
no more adapters available as accessories



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1			
Measuring range	-0.5...10 bar	-7...145 psi	-50...1000 kPa	-0.05...1 MPa
Process connection	threaded connection Aseptoflex external thread Aseptoflex			

Application

Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	150 bar	2175 psi	15000 kPa
Pressure rating	50 bar	725 psi	5000 kPa



Flush pressure transmitter

PM-010-RES30-E-ZVG/US/ /P

Type of pressure	relative pressure			
No dead space	yes			
Electrical data				
Operating voltage [V]	14...30 DC			
Min. insulation resistance [MΩ]	100; (500 V DC)			
Protection class	III			
Reverse polarity protection	yes			
Inputs / outputs				
Number of inputs and outputs	Number of analogue outputs: 1			
Outputs				
Total number of outputs	1			
Output signal	analogue signal			
Number of analogue outputs	1			
Analogue current output [mA]	4...20			
Max. load [Ω]	550; (Ub = 24 V; (Ub - 13 V) / 20 mA)			
Overload protection	yes			
Measuring/setting range				
Measuring range	-0.5...10 bar	-7...145 psi	-50...1000 kPa	-0.05...1 MPa
Analogue start point	-0.5...7.49 bar	-7...109 psi	-50...749 kPa	
Analogue end point	2...9.99 bar	29...145 psi	200...999 kPa	
In steps of	0.01 bar	1 psi	1 kPa	
Factory setting		ASP = 0.00 bar	AEP = 9.99 bar	
Accuracy / deviations				
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)			
Characteristics deviation [% of the span]	< ± 0,6; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)			
Linearity deviation [% of the span]	< ± 0,5; (Turn down 1:1)			
Hysteresis deviation [% of the span]	< ± 0,1; (Turn down 1:1)			
Long-term stability [% of the span]	< ± 0,1; (Turn down 1:1; per year)			
Temperature coefficient zero point [% of the span / 10 K]	< ± 0,1; (0...80 °C)			
Temperature coefficient span [% of the span / 10 K]	< ± 0,2; (0...80 °C)			
Response times				
Max. response time analogue output [ms]	3			
Software / programming				
Parameter setting options	zero point; span			
Interfaces				
Communication interface	EPS			

PM2054



Flush pressure transmitter

PM-010-RES30-E-ZVG/US/ /P

Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	1 GHz / accuracy < 2,5%
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	271

Mechanical data		
Weight	[g]	474.5
Materials		stainless steel (316L/1.4404); PEI; FKM
Materials (wetted parts)		ceramics (99.9 % Al2O3); stainless steel (316L/1.4404); surface characteristics: Ra < 0,4 / Rz 4; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection Aseptoflex external thread Aseptoflex

Remarks	
Remarks	The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.
Notes	Please do not use for new projects.; no more adapters available as accessories
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

