



# SM8601



## Magnetic-inductive flow meter

SMN11GGXFRKG/US-100

Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]		2
Permanent current rating of switching output DC [mA]		200
Number of analogue outputs		1
Analogue current output [mA]		4...20; (scalable)
Max. load [Ω]		500
Analogue voltage output [V]		0...10; (scalable)
Min. load resistance [Ω]		2000
Pulse output		flow rate meter
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

### Measuring/setting range

Measuring range	6...1584 gph	0.1...26.4 gpm
Display range	-1902...1902 gph	-31.7...31.7 gpm
Resolution	2 gph	0.05 gpm
Set point SP	14...1586 gph	0.25...26.4 gpm
Reset point rP	6...1578 gph	0.1...26.25 gpm
Analogue start point ASP	0...1272 gph	0...21.2 gpm
Analogue end point AEP	312...1586 gph	5.2...26.4 gpm
In steps of	2 gph	0.05 gpm

### Volumetric flow quantity monitoring

Pulse value		0.01...100 000 000 gal
Pulse length [s]		0,0025...2

### Temperature monitoring

Measuring range [°F]		-4...176
Resolution [°F]		0.5
Set point SP [°F]		-2.5...176
Reset point rP [°F]		-3.5...175
Analogue start point [°F]		-4...140.5
Analogue end point [°F]		31.5...176
In steps of [°F]		0.5

### Accuracy / deviations

#### Flow monitoring

Accuracy (in the measuring range)		± (0,8 % MW + 0,5 % MEW)
Repeatability		± 0,2% MEW

#### Temperature monitoring

Accuracy [K]		± 2,5 (Q > 0,26 gpm)
--------------	--	----------------------

# SM8601



## Magnetic-inductive flow meter

SMN11GGXFRKG/US-100

Response times	
Flow monitoring	
Response time [s]	0.15; (dAP = 0, T19)
Delay time programmable dS, dr [s]	0...50
Damping process value dAP [s]	0...5
Temperature monitoring	
Dynamic response T05 / T09 [s]	T09 = 20 (Q > 0,26 gpm)
Software / programming	
Parameter setting options	Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / normally closed; switching logic; current/voltage/pulse output; start-up delay; display can be deactivated; Display unit
Interfaces	
Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.1
SDCI standard	IEC 61131-9
Profiles	Smart Sensor - SSP 0      Generic Profiled Sensor
	Function      Device identification
	Function      Process data variable
	Function      Device diagnosis
SIO mode	yes
Required master port type	A
Process data analogue	3
Process data binary	2
Min. process cycle time [ms]	5
Supported DeviceIDs	<b>Type of operation</b> <b>DeviceID</b>
	default      576
Operating conditions	
Ambient temperature [°F]	14...140
Storage temperature [°F]	-13...176
Protection	IP 67
Tests / approvals	
EMC	DIN EN 60947-5-9
Shock resistance	DIN EN 60068-2-27      20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6      5 g (10...2000 Hz)
MTTF [years]	145
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data	
Weight [g]	698.5
Housing	cylindrical
Inlet pipe length	3 x DN
Outlet pipe length	1 x DN
Dimensions [mm]	Ø 54 / L = 110
Materials	stainless steel (316L/1.4404); PBT-GF20; PC; FKM; TPE

# SM8601



## Magnetic-inductive flow meter

SMN11GGXFRKG/US-100

Materials (wetted parts)	stainless steel (316L/1.4404); PEEK; FKM
Process connection	threaded connection 1" NPT internal thread DN25

### Displays / operating elements

Display	Display unit	6 x LED, green (gpm, gph, gal, °F, 10 <sup>3</sup> , 1000 x 10 <sup>3</sup> )
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit

### Remarks


Remarks	MW = measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection



- OUT1: colours to DIN EN 60947-5-2  
 switching output volumetric flow quantity monitoring  
 Pulse output quantity meter  
 signal output Preset counter  
 IO-Link
- OUT2: switching output volumetric flow quantity monitoring  
 switching output Temperature monitoring  
 analogue output volumetric flow quantity monitoring  
 analogue output Temperature monitoring  
 input counter reset  
 Core colours :
- BK = black  
 BN = brown  
 BU = blue  
 WH = white

# SM8601




## Magnetic-inductive flow meter

SMN11GGXFRKG/US-100

### Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity